



Eaton 101370

Eaton Moeller series xPole - PLI MCB.
Miniature circuit breaker (MCB) with plug-in
terminal, 16 A, 4p, characteristic: D

□□□□

PRODUCT NAME	Eaton Moeller series xPole - PLI MCB
CATALOG NUMBER	101370
PRODUCT LENGTH/DEPTH	84 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	70 mm
PRODUCT WEIGHT	0.409 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

□□□□

USED WITH	Miniature circuit breaker PLI
AMPERAGE RATING	16 A
FEATURES	Additional equipment possible
POLLUTION DEGREE	2
DEGREE OF PROTECTION	IP20
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT	8.8 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
TRIPPING CHARACTERISTIC	D
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT	0 W
WIDTH IN NUMBER OF MODULAR SPACINGS	4

□□

□□□	eaton-xpole-mmc4-6-m- mcb-wiring-diagram- 006.jpg
□□	eaton-xpole-pli-mcb- dimensions.jpg

VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Four-pole
RELEASE CHARACTERISTIC	D
TYPE	<ul style="list-style-type: none"> • Miniature circuit breaker • PLI
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
APPLICATION	<ul style="list-style-type: none"> • Switchgear for residential and commercial applications • xPole - Switchgear for residential and commercial applications
NUMBER OF POLES (PROTECTED)	4
NUMBER OF POLES (TOTAL)	4
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	16 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V	10 kA
RATED SWITCHING CAPACITY (IEC/EN 60898-1)	10 kA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
POWER LOSS	7.3 W

