



Eaton 100LR85

Eaton Bussmann series low voltage british standard fuse, 100A, AC 415 V, system C type II, 30 x 57 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	100LR85
PRODUCT LENGTH/DEPTH	57 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	101 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269

0000	
AMPERAGE RATING	100 A
CURRENT TYPE	AC
BREAKING CAPACITY	33 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	LR85
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
FUSE INDICATOR	Other
WATT LOSSES	5 W
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION	BS system C type II
CONSTRUCTION SIZE	23 x 57 mm
FUSE SHAPE	Cylindrical
VOLTAGE TYPE	AC
MATERIAL	Ceramic
RELEASE CHARACTERISTIC	Other
VOLTAGE RATING	415 V
TYPE	fuse
APPLICATION	protection of incoming cables into residential and commercial properties

00	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250979en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00: