



## Eaton 102304

Eaton Moeller series xEffect - FAZ-NA, FAZ-RT MCB. FAZ-RT, 3-pole, tripping characteristic: D, rated current In: 6 A



<b>PRODUCT NAME</b>	Eaton Moeller series xEffect - FAZ-NA, FAZ-RT MCB
<b>CATALOG NUMBER</b>	102304
<b>PRODUCT LENGTH/DEPTH</b>	105 mm
<b>PRODUCT HEIGHT</b>	75.5 mm
<b>PRODUCT WIDTH</b>	53.1 mm
<b>PRODUCT WEIGHT</b>	0.367 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC 60947-2 CSA (File No. 204453) UL (Category Control Number DIVQ) UL (File No. E235139) UL 489, CSA C22.2 No. 5 Specially designed for North America, suitable as BCPD North America (UL listed, CSA certified) CE marking CSA-C22.2 No. 5-09 CSA (Class No. 1432-01) UL 489 IEC/EN 60947-2 EN45545-2 IEC 61373



Powering Business Worldwide

<b>USED WITH</b>	Miniature circuit breaker FAZ-RT
<b>AMPERAGE RATING</b>	6 A
<b>VOLTAGE RATING</b>	277 V AC / 480 V AC
<b>FEATURES</b>	Additional equipment possible
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-xeffect-faz-na,-mcb-dimensions-003.jpg</a>
□□□	<a href="#">eaton-xpole-mmc4-6-m-mcb-wiring-diagram-005.jpg</a> <a href="#">eaton-mcb-xeffect-faz-na,-wiring-diagram-002.eps</a>
□□	<a href="#">eaton-xeffect-faz-na,-mcb-dimensions.jpg</a> <a href="#">eaton-mcb-xeffect-faz-na,-3d-drawing-002.eps</a>

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FRAME</b>	45 mm
<b>POLLUTION DEGREE</b>	2
<b>MOUNTING METHOD</b>	Top-hat rail IEC/EN 60715
<b>DEGREE OF PROTECTION</b>	IP20 (IEC) IP20 UL/CSA Type: - IP40 (when fitted)
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	3.5 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>TERMINAL PROTECTION</b>	Finger and hand touch safe, DGUV VS3, EN 50274
<b>TERMINALS (TOP AND BOTTOM)</b>	Twin-purpose terminals
<b>TRIPPING CHARACTERISTIC</b>	D
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	75 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	70.5 mm
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED)</b>	25 mm <sup>2</sup>

<b>- MAX</b>	
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1 mm <sup>2</sup>
<b>CURRENT LIMITING CLASS</b>	3
<b>ENCLOSURE WIDTH</b>	105 mm
<b>FREQUENCY RATING - MAX</b>	60 Hz
<b>FREQUENCY RATING - MIN</b>	50 Hz
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>	0 W
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	3
<b>VOLTAGE RATING (IEC/EN 60947-2)</b>	415 V
<b>VOLTAGE RATING (UL)</b>	480Y/277 V
<b>VOLTAGE RATING AT DC</b>	60 V DC
<b>VOLTAGE TYPE</b>	AC
<b>MOUNTING POSITION</b>	As required
<b>OVERVOLTAGE CATEGORY</b>	III
<b>NUMBER OF POLES</b>	Three-pole
<b>FUNCTIONS</b>	Current limiting circuit breaker
<b>LIFESPAN, ELECTRICAL</b>	20000 operations
<b>RELEASE CHARACTERISTIC</b>	D
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• FAZ-RT</li> <li>• Miniature circuit breaker</li> </ul>
<b>SPECIAL FEATURES</b>	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of

---

current carrying capacity

---

**APPLICATION**

- Feeder circuits, branch circuits
- Switchgear for industrial and advanced commercial applications
- xEffect - Switchgear for industrial and advanced commercial applications

---

**MOUNTING WIDTH** 17.7 mm

---

**SELECTIVITY CLASS** 3

---

**MOUNTING WIDTH PER POLE** 17.7 mm

---

**NUMBER OF POLES (PROTECTED)** 3

---

**NUMBER OF POLES (TOTAL)** 3

---

**RATED INSULATION VOLTAGE (UI)** 440 V

---

**RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)** 6 A

---

**RATED OPERATIONAL VOLTAGE (UE) - MAX** 415 V

---

**RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V** 15 kA

---

**RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V** 15 kA

---

**RATED SWITCHING CAPACITY (IEC/EN 60947-2)** 15 kA

---

**STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT** 0 W

---

**TIGHTENING TORQUE** UL: 2.4 Nm (21 lb-in) for AWG 18 - AWG 12  
UL: 4 Nm (36 lb-in) for AWG 6  
Max. 2.4 Nm  
UL: 2.8 Nm (25 lb-in) for AWG 10 - AWG 8

---

**POWER LOSS** 3.6 W

---

