



Eaton 101344

Eaton Moeller series xPole - PLI MCB.
Miniature circuit breaker (MCB) with plug-in
terminal, 4 A, 3p+N, characteristic: D

□□□□

| | |
|---------------------------------|---|
| PRODUCT NAME | Eaton Moeller series xPole - PLI MCB |
| CATALOG NUMBER | 101344 |
| PRODUCT LENGTH/DEPTH | 84 mm |
| PRODUCT HEIGHT | 75.5 mm |
| PRODUCT WIDTH | 70 mm |
| PRODUCT WEIGHT | 0.421 kg |
| COMPLIANCES | RoHS conform |



Powering Business Worldwide

□□□□

| | |
|--|--|
| USED WITH | Miniature circuit breaker PLI |
| AMPERAGE RATING | 4 A |
| FEATURES | Additional equipment possible Concurrently switching N- neutral |
| POLLUTION DEGREE | 2 |
| DEGREE OF PROTECTION | IP20 |
| EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT | 4.5 W |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) | 4 kV |
| TRIPPING CHARACTERISTIC | D |
| AMBIENT OPERATING TEMPERATURE - MAX | 75 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -25 °C |
| BUILT-IN DEPTH | 70.5 mm |
| CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX | 25 mm ² |
| CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN | 1 mm ² |
| CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX | 25 mm ² |
| CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN | 1 mm ² |
| CURRENT LIMITING CLASS | 3 |
| FREQUENCY RATING - MAX | 60 Hz |
| FREQUENCY RATING - MIN | 50 Hz |
| HEAT DISSIPATION CAPACITY | 0 W |
| HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT | 0 W |

□□

| | |
|-----|---|
| □□□ | eaton-xpole-mmc4-6-m- mcb-wiring-diagram- 004.jpg |
| □□ | eaton-xpole-pli-mcb- dimensions.jpg |

| | |
|--|--|
| WIDTH IN NUMBER OF MODULAR SPACINGS | 4 |
| VOLTAGE TYPE | AC |
| OVERVOLTAGE CATEGORY | III |
| NUMBER OF POLES | Three-pole + N |
| RELEASE CHARACTERISTIC | D |
| TYPE | <ul style="list-style-type: none"> • Miniature circuit breaker • PLI |
| SPECIAL FEATURES | Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity |
| APPLICATION | <ul style="list-style-type: none"> • Switchgear for residential and commercial applications • xPole - Switchgear for residential and commercial applications |
| NUMBER OF POLES (PROTECTED) | 3 |
| NUMBER OF POLES (TOTAL) | 4 |
| RATED INSULATION VOLTAGE (UI) | 440 V |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 4 A |
| RATED OPERATIONAL VOLTAGE (UE) - MAX | 400 V |
| RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V | 10 kA |
| RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V | 10 kA |
| RATED SWITCHING CAPACITY (IEC/EN 60898-1) | 10 kA |
| STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT | 0 W |
| POWER LOSS | 4.7 W |

