



Eaton 106847

Eaton Moeller® series LSR Hasp-operated safety switch, LSR, Hasp-operated safety switch, Complete unit, 1 N/O, 1 NC, Insulated material, Screw terminal, -25 - +70 °C

□□□□

PRODUCT NAME	Eaton Moeller® series LSR Hasp-operated safety switch
CATALOG NUMBER	106847
PRODUCT LENGTH/DEPTH	33 mm
PRODUCT HEIGHT	160 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	0.094 kg
CERTIFICATIONS	IEC/EN 60947-5 CE CSA CSA Class No.: 3211-03 UL 508 CSA File No.: 012528 UL IEC/EN 60947 UL Category Control No.: NKCR UL File No.: E29184 CSA-C22.2 No. 14
CATALOG NOTES	Contacts with safety function, by positive opening to IEC/EN 60947-5-1



Powering Business Worldwide

TYPE	• Position switch
	• Safety position switch

FEATURES	Forced opening
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

DECLARATIONS OF CONFORMITY	eaton-hasp-operated-safety-switch-declaration-of-conformity-uk251048en.pdf
----------------------------	--

00000	IL05208006Z
000	eaton-position-switches-contact-lsr-hinge-operated-safety-switch-wiring-diagram-002.eps
00000	eaton-position-switches-diagram-lsr-hasp-operated-safety-switch-contact-travel-diagram-002.eps
00	eaton-position-switches-switch-lsr-hasp-operated-safety-switch-dimensions.eps eaton-general-certificate-lsr-hasp-operated-safety-switch-standards.eps

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ELECTRIC CONNECTION TYPE	Cable entry metrical
ENCLOSURE MATERIAL FINISHING	Other
OPERATING FREQUENCY	1800 Operations/h
ACTUATOR ALIGNMENT	Other
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
ENCLOSURE MATERIAL	Plastic Insulated material
ENCLOSURE TYPE	Cuboid
RATED OPERATIONAL CURRENT (IE) AT DC-13, 110 V	0.8 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 125 V	0.3 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V	0.3 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	3 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	6 A

SENSOR HEIGHT	91 mm
SENSOR LENGTH	32 mm
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
WIDTH SENSOR	30 mm
PRODUCT CATEGORY	Hasp-operated safety switch
ACTION	2021118113756-Mechanical Limit Switches.xlsm-Data
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
EXPLOSION SAFETY CATEGORY FOR DUST	None
EXPLOSION SAFETY CATEGORY FOR GAS	None
ACTUATOR TYPE	Rotary lever
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
DIAMETER SENSOR	0 mm
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0.13 W
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF SAFETY AUXILIARY CONTACTS	0
RATED INSULATION VOLTAGE (UI)	500 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 125 V	6 A
RATED OPERATIONAL CURRENT (IE) AT AC-15,	6 A

220 V, 230 V, 240 V	
RATED OPERATIONAL CURRENT (IE) AT AC-15, 24 V	6 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	4 A
MOUNTING POSITION	As required
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
CONNECTION TYPE	Screw terminal
DEGREE OF PROTECTION	IP65 NEMA Other
INTERFACE TYPE	None
SWITCH FUNCTION TYPE	Slow-action switch
LIFESPAN	1,000,000 mechanical Operations
REPETITION ACCURACY	0.02 mm (Contacts/switching capacity)
SHOCK RESISTANCE	25 g, Standard-action contact, Mechanical, Half-sinusoidal shock 20 ms
SUPPLY FREQUENCY	Max. 400 Hz, Contacts
SUITABLE FOR	Safety functions
SHORT-CIRCUIT PROTECTION RATING	Max. 6 A gG/gL, Fuse, Contacts
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	2 x (0.5 - 1.5) mm ² 1 x (0.5 - 1.5) mm ²
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 2.5) mm ² 2 x (0.75 - 1.5) mm ²

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

