

Eaton 103098

Eaton xComfort BF LV systems Final Distribution Boards. Complete flush-mounted flat distribution board, white, 33 SU per row, 5 rows, type C

PRODUCT NAME	Eaton xComfort BF small distribution board
CATALOG NUMBER	103098
PRODUCT LENGTH/DEPTH	140 mm
PRODUCT HEIGHT	930 mm
PRODUCT WIDTH	760 mm
PRODUCT WEIGHT	18.6 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 62208 IEC/EN 61439-3 IEC/EN 61439-1

USED WITH	Basic device
	Installation distribution board BF flat distribution board
SPECIAL FEATURES	<ul style="list-style-type: none"> • IP30 • Protection Class I • Steel sheet enclosure gray (RAL 7035)
TYPE	<ul style="list-style-type: none"> • Basic device • BF flat DBO • Installation distribution boards
FEATURES	EMC-version Earthing terminal block Neutral terminal block
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility.
10.13 MECHANICAL FUNCTION	Meets the product standard's requirements.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Not relevant to indoor installations.
10.2.5 LIFTING	Does not apply to enclosures without lifting

eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf
eaton-xcomfort-bf-lv-systems-dimensions-004.eps

	aids.
10.2.6 MECHANICAL IMPACT	IK07
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	IP30
10.4 CLEARANCES AND CREEPAGE DISTANCES	Is the panel builder's responsibility.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	< 0.1 Ω ; meets the product standard's requirements.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Is the panel builder's responsibility.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Ui = 415 V AC
10.9.3 IMPULSE WITHSTAND VOLTAGE	Does not apply to basic enclosures as defined in EN 62208.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Does not apply to metal enclosures.
FITTED WITH:	DIN rail mounting frame Front plates Wall trough with door frame Door with three-point turn-lock Neutral-/protective conductor terminal
ENCLOSURE MATERIAL	Steel
BUILT-IN HEIGHT	0 mm
BUILT-IN WIDTH	720 mm
CABLE ENTRY POSTION	Cable entries on top and bottom
TERMINAL TYPE	Screw terminals
BUILT-IN DEPTH	127 mm
HEAT DISS. AMBIENT 35°C DELTA T:20°C FLUSH MOUNT INDIVID. ENCL. TOP(IEC 60890)	68 W

HEAT DISS. AMBIENT 35°C DELTA T:35°C FLUSH MOUNT INDIVID. ENCL. TOP(IEC 60890)	136 W
CLOSURE TYPE	Other
COVER/DOOR COLOR	White
COVER/DOOR MODEL	Closed
COVER/DOOR TYPE	Door Single
RAL-NUMBER	9016
WIDTH IN NUMBER OF MODULAR SPACINGS	33
AMBIENT OPERATING TEMPERATURE DETAILS	-5 °C - 40 °C
APPLICATION	Indoor (installation site)
VOLTAGE RATING AT AC	415 V AC
COLOR	Traffic white (RAL 9016) White
NUMBER OF ROWS	5
FREQUENCY RATING OF CONTACTS	50 Hz / 60 Hz
MODULE RACK TYPE	Rail frame
DEGREE OF PROTECTION	IP30 IK07 (impact resistance)
NUMBER OF MODULE SPACE UNITS PER ROW	33
PROTECTION CLASS	I (earthed)
PROTECTIVE SHROUDING MATERIAL	Metal
FUNCTIONS	Basic device Sealable
MATERIAL	Sheet steel, powder- coated
MOUNTING METHOD	Flush mounted (plaster) Flush mounting DIN-rail Hollow-wall mounting and flush mounting
INTERNAL DEPTH	127 mm
PE AND N TERMINAL NUMBER AND CROSS SECTION	PE: 2 x 25 mm ² + 58 x 16 mm ² N: 2 x 25 mm ² + 58 x 16 mm ²
NUMBER OF OPENINGS FOR SOCKET OUTLETS	0

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

