

Eaton 107940

Eaton Moeller® series M22 Contact element, Cage Clamp, Front fixing, 1 N/O, 1 NC, 24 V 3 A, 220 V 230 V 240 V 4 A

PRODUCT NAME	Eaton Moeller® series M22 Accessory Contact element
CATALOG NUMBER	107940
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	38 mm
PRODUCT WEIGHT	0.012 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CSA Std. C22.2 No. 94-91 IEC 60947-5 CSA Std. C22.2 No. 14-05 EN 60947-5 UL 508 CSA IEC 60947-5-1 CSA File No.: 012528 UL File No.: E29184 CE CSA-C22.2 No. 94-91 UL Category Control No.: NKCR CSA Class No.: 3211-03 IEC/EN 60947-5 IEC CSA-C22.2 No. 14-05 UL/CSA UL

USED WITH

Can be used with NZM1 circuit-breaker: a standard auxiliary contact can be clipped into the circuit-breaker.

Can be used with NZM4 circuit-breaker: up to two standard auxiliary contacts can be clipped into the circuit-breaker.

Can be used with NZM3, 4 circuit-breaker: up to three standard auxiliary contacts can be clipped into the circuit-breaker.

Can be used with NZM1, 2, 3 circuit-breaker: a trip-indicating auxiliary contact can be clipped into the circuit-breaker.

Can be used with NZM2 size circuit-breaker: a standard auxiliary contact can be clipped into the circuit-breaker.

TYPE

Auxiliary contact

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
ELECTRIC CONNECTION TYPE	Spring clamp connection
OPERATING FREQUENCY	3600 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC

	60068-2-30 Damp heat, constant, to IEC 60068-2-78
ACTUATING FORCE - MAX	10 N
ACTUATOR TRAVEL AND ACTUATION FORCE (DIN EN 60947-5-1)	4.8 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	85 °C
AMBIENT STORAGE TEMPERATURE - MIN	-25 °C
CONVENTIONAL THERMAL CURRENT ITH OF AUXILIARY CONTACTS (1-POLE, OPEN)	4 A
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	20 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	0.05 W
KNOB TRAVEL	5.7 mm
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF SWITCHES (FAULT SIGNAL)	0
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
CONTACT CONFIGURATION	1 NO, 1 NC

RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
CONNECTION TYPE	Double contact Front fixing Cage Clamp
MOUNTING METHOD	Front fastening
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 5,000,000 switching operations (statistically determined, at 5 V DC/1 mA) 1 failure per 10,000,000 switching operations (Statistically determined, at 24 V DC/5 mA)
DEGREE OF PROTECTION	IP20
MODEL	Top mounting and integrable
LAMP HOLDER	None
TERMINAL CAPACITY (AWG)	1 x (20 - 18) 2 x (20 - 18)
TERMINAL CAPACITY (SOLID/FLEXIBLE WITH FERRULE)	2 x (0,5 - 0,75) mm ² 1 x (0,5 - 1,5) mm ²
TERMINAL CAPACITY (STRANDED)	0.5 - 1.5 mm ²
SHORT-CIRCUIT PROTECTION	PKZM0-10/FAZ-B6/1, Contacts, Max. short-circuit protective device, Fuseless
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
PRODUCT CATEGORY	Accessories
SHORT-CIRCUIT PROTECTION RATING	Max. 10 A gG/gL, Fuse, Contacts Max. 10 A gG/gL, Fuse, Auxiliary contacts
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 115 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	6 A

RATED OPERATIONAL CURRENT (IE) AT DC-13, 110 V	0.6 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V	0.3 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	3 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 60 V	1 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	4 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	230 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	220 V
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	0.5 - 1.5 mm ²
TERMINAL CAPACITY (SOLID)	0.5 - 1.5 mm ²



**DECLARATIONS
OF
CONFORMITY**

[eaton-accessory-declaration-of-conformity-uk251351en.pdf](#)

MCAD MODEL

[doppelkontaktelement_cage_front.stp](#)

[IL04716002Z](#)

[eaton-operating-contact-m22-contact-element-wiring-diagram-006.eps](#)

[eaton-circuit-breaker-diagram-m22-contact-element-wiring-diagram.eps](#)

[eaton-circuit-breaker-contact-m22-contact-element-wiring-diagram-002.eps](#)

[eaton-operating-diagram-m22-contact-element-contact-travel-diagram-005.eps](#)

[eaton-operating-actuation-m22-contact-element-dimensions.eps](#)

[eaton-operating-rmq-m22-contact-
element-3d-drawing.eps](#)

/

[RMQ small E-Stop emergency-stop
button](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

