



Eaton 104609

Eaton Moeller series NZM Earth-fault release, 30mA, 3p, bottom

□□□□

PRODUCT NAME	Eaton Moeller series NZM Earth leakage relay
CATALOG NUMBER	104609
PRODUCT LENGTH/DEPTH	180 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.9 kg
COMPLIANCES	IEC RoHS conform
CERTIFICATIONS	IEC/EN 60947-2 IEC/EN 60947-2 annex B

USED WITH	NZM1 Three-pole N(S)1
VOLTAGE RATING	200 - 415 V AC, min. 80 V AC for detection of fault currents type A/AC (dependent on mains voltage)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.

□□□□□	eaton-residual-current- module-mount-below- nzm1-il01219027z.pdf
□□	eaton-circuit-breaker- release-nzm-earth-fault- release-dimensions.eps eaton-circuit-breaker- symbol-nzm-earth-fault- release-symbol.eps eaton-circuit-breaker- release-nzm-earth-fault- release-3d-drawing- 002.eps

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FRAME	NZM1 45 mm
FREQUENCY RATING	50 Hz / 60 Hz
LIFESPAN, MECHANICAL	20000 operations
MOUNTING METHOD	Bottom
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
CURRENT RATING - MAX	100 A
POWER ON-DELAY TIME - MAX	30 ms
POWER ON-DELAY TIME - MIN	30 ms
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	415 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	200 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	415 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60	200 V

HZ - MIN	
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
CURRENT RATING - MIN	15 A
DEGREE OF PROTECTION	IP20 (operating component area)
MOUNTING POSITION	Vertical and 90° in all directions
FAULT CURRENT DETECTION RANGE	50/60 Hz
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (SOLID/FLEXIBLE CONDUCTOR)	As NZM1 standard terminal with ferrules As NZM1 standard terminal without ferrules
TYPE	Accessory Earth-fault releases
SPECIAL FEATURES	Earth-fault release to IEC/EN 60947-2 Not UL/CSA approved Suitable for use in three-phase systems Pulse-current sensitive type A according to core-balance principle For 3 pole NZM1 circuit-breakers and N1 switch-disconnectors Supply voltage-dependent Ue = 200 – 415 V 50/60 Hz Control knobs, sealable. Bottom mounting up to 100 A
APPLICATION	In three-phase systems
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
RATED FAULT CURRENT - MAX	0.03 A
RATED FAULT CURRENT - MIN	0.03 A
RATED OPERATING VOLTAGE (UE) - MAX	415 V
SENSITIVITY TYPE	Pulse-current sensitive as per core-balance principle (type A)

