



## Eaton 106402

Eaton EC4P Compact PLC, 24 V DC, 12DI(of 4AI), 6DO(R), ethernet, CAN

### □□□□

|                             |   |
|-----------------------------|---|
| <b>PRODUCT NAME</b>         | Eaton EC4P Compact PLC  |
| <b>CATALOG NUMBER</b>       | 106402  |
| <b>PRODUCT LENGTH/DEPTH</b> | 72 mm   |
| <b>PRODUCT HEIGHT</b>       | 90 mm   |
| <b>PRODUCT WIDTH</b>        | 107.5 mm  |
| <b>PRODUCT WEIGHT</b>       | 0.351 kg  |
| <b>CERTIFICATIONS</b>       | CSA File No.: 012528<br>UL508<br>UL<br>UL File No.: E135462<br>CSA Class No.: 2252-01<br>CE<br>CSA-C22.2 No. 142-M<br>IEC/EN 61000-4-2, Level 3<br>UL Category Control No.:<br>NRAQ<br>CSA-C22.2 No. 0-M<br>CSA |
| <b>CATALOG NOTES</b>        | Expandable:<br>Inputs/outputs and bus<br>systems  |

**FEATURES** Asynchronous, cyclic, acyclic PDO types (operating modes of the slave)  
190 received bytes in a block (PRG interface RS232, Master mode)

**AIR DISCHARGE** 8 kV

**10.10 TEMPERATURE RISE** The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**10.11 SHORT-CIRCUIT RATING** Is the panel builder's responsibility.

**10.12 ELECTROMAGNETIC COMPATIBILITY** Is the panel builder's responsibility.

**10.13 MECHANICAL FUNCTION** The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

**10.2.2 CORROSION RESISTANCE** Meets the product standard's requirements.

**10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES** Meets the product standard's requirements.

**10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT** Meets the product standard's requirements.

**10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS** Meets the product standard's requirements.

**10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION** Meets the product standard's requirements.

**10.2.5 LIFTING** Does not apply, since the entire switchgear needs to be evaluated.

**10.2.6 MECHANICAL IMPACT** Does not apply, since the entire switchgear needs to be evaluated.

**10.2.7 INSCRIPTIONS** Meets the product standard's requirements.

**10.3 DEGREE OF PROTECTION OF ASSEMBLIES** Meets the product standard's requirements.

**10.4 CLEARANCES AND** Meets the product

**CHARACTERISTIC CURVE** [eaton-electrical-timers-easy-control-relays-characteristic-curve.eps](#)

□□□□□ [IL05003003Z](#)

**□□** [eaton-modular-plc-easy-module-ec4p-compact-plc-dimensions.eps](#)

[eaton-general-approval-easy-control-relays-standards.jpg](#)

|   |  |
|---|--|
| <b>CREEPAGE DISTANCES</b>                                       | standard's requirements.   |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.   |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.   |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.   |
| <b>FITTED WITH:</b>   | Power supply<br>Memory unit<br>Basic device<br>Digital input module<br>Libraries<br>Engineering software<br>Function module<br>easyNet/CANopen® on board<br>Digital output module<br>Documentation<br>Other components<br>Communication module<br>Analog input module<br>Ethernet on board |
| <b>POLLUTION DEGREE</b>   | 2  |
| <b>ACCURACY</b>   | $\pm 5$ s/day ( $\pm 0.5$ h/year),<br>Real-time clock, normally<br>$\pm 3$ %, of actual value, two devices (Analog Inputs)<br>$\pm 2$ , (I7, I8, I11, I12) $\pm 0.12$ V, of actual value, within a single device (Analog Inputs)   |
| <b>BURST IMPULSE</b>  | 2 kV, Supply cable<br>According to IEC/EN 61000-4-4, level 3<br>2 kV, Signal cable   |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 6 kV (contact-coil)  |
| <b>UTILIZATION CATEGORY</b>                                     | B 300 Light Pilot Duty,<br>UL/CSA Control Circuit<br>Rating Codes AC   |

|                                     |   |
|-------------------------------------|---|
|                                     | R 300 Light Pilot Duty,<br>UL/CSA Control Circuit<br>Rating Codes DC  |
| <b>AIR PRESSURE</b>                 | 1080 hPa (operation)  |
| <b>BUS TERMINATION</b>              | EASY-NT-R plug (incl. bus<br>terminating resistor 120<br>Ω),first and last station,<br>CANopen®   |
| <b>ENVIRONMENTAL<br/>CONDITIONS</b> | Condensation: prevent<br>with appropriate<br>measures<br>Clearance in air and<br>creepage distances<br>according to EN 50178, UL<br>508, CSA C22.2, No. 142 |
| <b>INDICATION</b>                   | LCD-display used as status<br>indication of Digital inputs<br>24 V DC   |
| <b>INPUT</b>                        | Voltage (DC)  |
| <b>CABLE LENGTH</b>                 | 30 m, screened, Analog<br>inputs<br>100 m, unshielded, Digital<br>inputs 24 V DC  |
| <b>MOUNTING METHOD</b>              | Top-hat rail fixing<br>(according to IEC/EN<br>60715, 35 mm)<br>Screw fixing using fixing<br>brackets ZB4-101-GF1<br>(accessories)                          |
| <b>NUMBER OF OUTPUTS</b>            | 6 (relay outputs)<br>8 Transistor Outputs<br>Relay outputs in groups of<br>1  |
| <b>CHARACTER FORMATS</b>            | 8E1, 8O1, 8N1, 8N2, 7E2,<br>7O2, 7N2, 7E1, PRG<br>interface RS232, Master<br>mode   |
| <b>SCREWDRIVER SIZE</b>             | 3.5 x 0.8 mm, Terminal<br>screw   |
| <b>MOUNTING POSITION</b>            | Vertical<br>Horizontal  |
| <b>CONTACT DISCHARGE</b>            | 6 kV, Electrostatic<br>discharge (ESD)  |
| <b>OVERVOLTAGE<br/>CATEGORY</b>     | II  |
| <b>CONNECTION TYPE</b>              | RJ45, PRG Interface RS232<br>2 x RJ45, 8 pole,<br>CANopen®<br>RJ45, Ethernet  |
| <b>CONSTANT<br/>ACCELERATION</b>    | 2 g, 57 - 150 Hz, according<br>to IEC/EN 60068-2-6,<br>Vibrations   |
| <b>CONSTANT AMPLITUDE</b>           | 0,15 mm, 10 - 57 Hz,  |

|  |  |
|--|--|
|  | according to IEC/EN 60068-2-6, Vibrations  |
| <b>SURGE RATING</b>                                  | 2 kV, Supply cables, symmetrical, EASY...AC, power pulses (Surge), EMC<br><br>According to IEC/EN 61000-4-5, power pulses (Surge), EMC<br>0.5 kV, Supply cables, symmetrical, EASY...DC, power pulses (Surge), EMC   |
| <b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE AWG)</b> | 22 - 12  |
| <b>CONVERSIONS</b>                                   | Each CPU cycle, Analog inputs  |
| <b>ELECTROMAGNETIC FIELDS</b>                        | 10 V/m (according to IEC EN 61000-4-3)   |
| <b>TERMINAL CAPACITY (SOLID AWG)</b>                 | 22 - 12  |
| <b>NUMBER OF INPUTS (ANALOG)</b>                     | 4 (I7, I8, I11, I12)   |
| <b>CYCLE TIME</b>                                    | < 0.3 ms, for 1 k of instructions (Bit, Byte), CPU   |
| <b>NUMBER OF MODULES</b>                             | Max. 126 (slaves)  |
| <b>DROP AND TOPPLE</b>                               | 50 mm Drop height, Drop to IEC/EN 60068-2-31   |
| <b>IMMUNITY TO LINE-CONDUCTED INTERFERENCE</b>       | 10 V (according to IEC/EN 61000-4-6)   |
| <b>RADIO INTERFERENCE CLASS</b>                      | Class B (EN 55011)<br>Class B (EN 55022)   |
| <b>DATA TRANSFER RATE</b>                            | 0.6 kBit/s, PRG interface<br>RS232, Master mode<br>500 kBit/s at 25 m, CANopen®<br>1.2 kBit/s, PRG interface<br>RS232, Master mode<br>57.6 kBit/s, PRG interface<br>RS232, Master mode<br>4.8 kBit/s, PRG interface<br>RS232, Master mode<br>19.2 kBit/s, PRG interface<br>RS232, Master mode<br>0.3 kBit/s, PRG interface<br>RS232, Master mode<br>10 MBit/s, 100 m, Ethernet<br><br>2.4 kBit/s, PRG interface<br>RS232, Master mode<br>10 kBit/s at 1000 m , CANopen®<br>250 kBit/s at 60 m, |

|                                   |   |
|-----------------------------------|---|
|                                   | CANopen®<br>9.6 kBit/s, PRG interface<br>RS232, Master mode<br>38.4 kBit/s, PRG interface<br>RS232, Master mode<br>125 kBit/s at 125 m,<br>CANopen®<br>50 kBit/s at 300 m,<br>CANopen®<br>20 kBit/s at 700 m,<br>CANopen® |
| <b>RELATIVE HUMIDITY</b>          | 5 - 95 % (non-condensing)   |
| <b>DEGREE OF PROTECTION</b>       | IP20  |
| <b>SAFE ISOLATION</b>             | 300 V AC, Between coil<br>and contact, According to<br>EN 50178<br>300 V AC, Between two<br>contacts, According to EN<br>50178  |
| <b>DELAY TIME</b>                 | 0.25 ms typ., Digital inputs<br>24 DC (I5 - I12), Delay time<br>from 0 to 1<br>0.02 ms typ., Digital inputs<br>24 DC (I1 - I4), Delay time<br>from 0 to 1   |
| <b>RESIDUAL RIPPLE</b>            | ≤ 5 %   |
| <b>RAPID COUNTER INPUTS</b>       | 2 (I1, I2) at 16 Bit or 1 (I1)<br>at 32 Bit<br>16/32 Bit (value range)<br>≤ 20 m (cable length,<br>screened)<br>50 kHz, Counter frequency<br><br>Square (pulse shape)   |
| <b>INSULATION RESISTANCE</b>      | According to EN 50178   |
| <b>FUNCTIONS</b>                  | Building blocks   |
| <b>HEAT DISSIPATION</b>           | 3.4 W   |
| <b>SUPPLY VOLTAGE AT DC - MAX</b> | 24 VDC  |
| <b>RESOLUTION</b>                 | <ul style="list-style-type: none"> <li>• 0.01 V analog (Analog inputs)</li> <li>• 0.01 V digital (Analog inputs)</li> <li>• 10 Bit (value 0 - 1023, Analog inputs)</li> </ul>   |
| <b>INCREMENTAL COUNTER</b>        | Counter inputs: I1, I2<br>Counter frequency: ≤ 40 kHz<br>Reference input: I3<br>Signal offset: 90°<br>Number of counter inputs:<br>1 (I1, I2, I3, I4)   |

|                                |   |
|--------------------------------|---|
|                                | Input for reference switch:<br>I4<br>Pulse shape: Square<br>Value range: 32 Bit   |
| <b>STATION</b>                 | To DS 301 V4, Control contact rated current, Mode slave, Interfaces   |
| <b>INPUT CURRENT</b>           | 2.2 mA (I7 - I8, at 24 V DC, at signal 1)<br>3.3 mA (I1 - I6, at 24 V DC, at signal 1)<br>140 mA<br>3.3 mA (I9 - I10, at 24 V DC, at signal 1)<br>2.2 mA (I11 - I12, at 24 V DC, at signal 1)<br>1 mA (Analog inputs)   |
| <b>INPUT IMPEDANCE</b>         | 11.2 kΩ   |
| <b>INPUT VOLTAGE</b>           | Signal 0: < 5 V DC (I1 - I6, I9 - I10, Digital inputs, 24 V DC)<br>Signal 1: > 8 V DC (I7 - I8, I11 - I12, Digital inputs, 24 V DC)<br>Signal 1: > 15 V DC (I1 - I6, I9 - I10, Digital inputs, 24 V DC)<br>Signal 0: < 8 V DC (I7 - I8, I11 - I12, Digital inputs, 24 V DC) |
| <b>PROCESSOR</b>               | Infineon XC161  |
| <b>SHOCK RESISTANCE</b>        | 15 g, Mechanical,<br>according to IEC/EN<br>60068-2-27, Half-sinusoidal shock 11 ms, 18 Impacts   |
| <b>INSCRIPTION</b>             | Individual inscription possible with EC4-COMBINATION-*  |
| <b>RATED BREAKING CAPACITY</b> | 200000 Operations at DC-13, 24 V DC, 1 A (500 Ops./h)<br>300000 Operations at AC-15, 250 V AC, 3 A (600 Ops./h)   |
| <b>LIFESPAN, ELECTRICAL</b>    | 25,000 Operations<br>(Fluorescent lamp load 1 x 58 W at 230/240 V AC, conventional, compensated)<br>25,000 Operations<br>(Fluorescent lamp load 10 x 58 W at 230/240 V AC, uncompensated)<br>25,000 Operations<br>(Filament bulb load at 500                                |

|                                   |  |
|-----------------------------------|--|
|                                   | W, 115/120 V AC)<br>25,000 Operations<br>(Fluorescent lamp load 10<br>x 58 W at 230/240 V AC,<br>with upstream electrical<br>device)<br>25,000 Operations<br>(Filament bulb load at<br>1000 W, 230/240 V AC)   |
| <b>SIGNAL RANGE</b>               | 0 - 10 V DC, Analog inputs   |
| <b>LIFESPAN, MECHANICAL</b>       | 10,000,000 Operations<br>10,000,000 Operations<br>(Relay outputs)  |
| <b>MAKING/BREAKING CAPACITY</b>   | 3600/360 VA (AC, at B 300)<br>28/28 VA (DC, at R 300)  |
| <b>MEMORY</b>                     | 8 kByte Retain Memory<br>4 kByte Input Memory<br>256 kByte Program<br>memory code<br>16 kByte Marker Memory<br>4 kByte Output Memory<br>14 segments of 16 kByte<br>Program memory data   |
| <b>NUMBER OF BYTES</b>            | 190 transmission bytes (in<br>a block)   |
| <b>NUMBER OF INPUTS (DIGITAL)</b> | 12 (24 V DC)<br>4 (I7, I8, I11, I12, can also<br>be used as analog inputs)<br>12<br>4 (can also be used as<br>analog inputs)   |
| <b>PARALLEL SWITCHING</b>         | Not permitted  |
| <b>VOLTAGE DIPS</b>               | ≤ 10 ms<br>According to EN 61131-2   |
| <b>UNINTERRUPTED CURRENT</b>      | 10 A AC, at 240 V AC<br>(UL/CSA)<br>5 A AC, max. thermal<br>continuous current $\cos \phi$<br>= 1 at B 300 (UL/CSA)<br>8 A DC, at 24 V DC<br>(UL/CSA)<br>1 A DC, at R 300 (UL/CSA)   |
| <b>POTENTIAL ISOLATION</b>        | Basic isolation: 600 V AC<br>(Relay outputs)<br>Between Digital inputs 24<br>V DC and Outputs: yes<br>Between Relay outputs<br>and Inputs: yes<br>Between Digital inputs 24<br>V DC and network<br>easyNet, easyLink<br>In groups (Relay outputs)<br>Between Relay outputs<br>and Power supply: yes<br>Between Analog inputs<br>and Outputs: yes |



|  |  |
|--|--|
|  | Between Analog inputs and Interface/memory card: no<br>Safe isolation according to EN 50178: 300 V AC (Relay outputs)  |
| <b>PROTECTION OF AN OUTPUT RELAY</b>   | Miniature circuit-breaker B16 or fuse 8 A (slow)   |
| <b>RATED OPERATIONAL VOLTAGE</b>   | 20.4 - 28.8 V DC<br>24 V DC (-15 %/+ 20 % - power supply)  |
| <b>RELAY OUTPUT</b>  | > 500 mA (Recommended for load: 12 V AC/DC)  |
| <b>SHORT-CIRCUIT PROTECTION</b>  | 16 A, Short-circuit-proof<br>$\cos \phi = 1$ , characteristic B16 at 600 A, Contacts, Relay outputs<br>16 A, Short-circuit-proof<br>$\cos \phi = 0.5$ to 0.7, characteristic B16 at 900 A, Contacts, Relay outputs |
| <b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)</b>                             | 0.2/2.5 mm <sup>2</sup>  |
| <b>SWITCHING FREQUENCY</b>   | 10 Hz, Relay outputs<br>2 Hz, Resistive load/lamp load, Relay outputs<br>0.5 Hz, Inductive load, Relay outputs   |
| <b>TERMINAL CAPACITY (SOLID)</b>   | 0.2/4 mm <sup>2</sup>  |
| <b>TIGHTENING TORQUE</b>   | 0.6 Nm   |
| <b>WRITE CYCLES OF THE RETENTIVE MEMORY</b>                                  | 10,000,000,000 read-write cycles   |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                                   | 55 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                                   | -25 °C   |
| <b>AMBIENT STORAGE TEMPERATURE - MAX</b>                                     | 70 °C  |
| <b>AMBIENT STORAGE TEMPERATURE - MIN</b>                                     | -40 °C   |
| <b>CONVENTIONAL THERMAL CURRENT ITH OF AUXILIARY CONTACTS (1-POLE, OPEN)</b> | 8 A  |
| <b>DISPLAY TEMPERATURE - MAX</b>   | 55 °C  |
| <b>DISPLAY TEMPERATURE - MIN</b>   | 0 °C   |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>                    | 0 W  |

|   |       |
|---|-------|
| HEAT DISSIPATION CAPACITY PDISS                               | 0 W   |
| HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID             | 0 W   |
| HEIGHT OF FALL (IEC/EN 60068-2-32) - MAX                      | 1 m   |
| RATED INSULATION VOLTAGE (UI)                                 | 250 V |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 0 A   |
| RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX                    | 300 V |
| RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX                    | 300 V |
| STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS            | 3.4 W |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



0000  
Eaton House  
30 Pembroke Road  
Dublin 4, 0000  
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

