



Eaton 110EET

Eaton Bussmann series high speed British standard fuse, Double barrel, 110A, 690 VAC/500 VDC (IEC), 700 VAC/500 VDC (UL), Class aR, Breaking capacity 200 kA RMS Sym.HS, 50 kA DC at 500 VDC

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	110EET
UPC	051712830522
PRODUCT LENGTH/DEPTH	94 mm
PRODUCT HEIGHT	36 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	91.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated Designed and tested to BS88 part 4 IEC 60269-4

□□□□

AMPERAGE RATING	110 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	71 mm
MOUNTING DIMENSION	M8
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I ₂ T)	4000 at 415 V, 6500 at 660 V
WATT LOSSES	27 W
FUSE SHAPE	Offset bolted tags
PRE ARC (I ₂ T)	600
COLOR	None
INTERRUPT RATING	200 kA RMS Sym, 50 kA at 500 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	EET
SUITABLE FOR	EC-600 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250921en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

