

# Eaton 107025

Eaton Moeller® series DIUL Reversing  
contactor combination, 380 V 400 V: 11 kW,  
24 V DC, DC operation

<b>PRODUCT NAME</b>	Eaton Moeller® series DIUL contactor combination
<b>CATALOG NUMBER</b>	107025
<b>PRODUCT LENGTH/DEPTH</b>	138 mm
<b>PRODUCT HEIGHT</b>	85 mm
<b>PRODUCT WIDTH</b>	90 mm
<b>PRODUCT WEIGHT</b>	1.24 kg
<b>CERTIFICATIONS</b>	CSA-C22.2 No. 60947-4-1- 14 UL Category Control No.: NLDX CE CSA Class No.: 2411-03, 3211-04 CSA UL 60947-4-1 UL CSA File No.: 012528 IEC/EN 60947-4-1 UL File No.: E29096
<b>CATALOG NOTES</b>	IE3-ready devices are identified by the logo on their packaging.

<b>ELECTRICAL CONNECTION TYPE FOR AUXILIARY- AND CONTROL-CURRENT CIRCUIT</b>	
	Screw connection
<b>NUMBER OF POLES</b>	Three-pole
<b>FEATURES</b>	Mechanical interlock
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL</b>	Does not apply, since the

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-contactor-combination-declaration-of-conformity-uk251248en.pdf</a>
<b>MCAD MODEL</b>	<a href="#">diulm17_25_32.dwg</a> <a href="#">diulm17_25_32.stp</a>
	<a href="#">IL03407030Z</a> <a href="#">IL03407044Z</a>

<b>IMPACT</b>	entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>UTILIZATION CATEGORY</b>	AC-3: Normal AC induction motors: starting, switch off during running AC-4: Normal AC induction motors: starting, plugging, reversing, inching
<b>CONNECTION</b>	Screw terminals
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	60 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	80 °C
<b>AMBIENT STORAGE</b>	-40 °C

<b>TEMPERATURE - MIN</b>	
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	5.3 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	1.8 W
<b>APPLICATION</b>	Contactor combinations for starting motors with two directions of rotation
<b>PRODUCT CATEGORY</b>	Contactor combinations
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>VOLTAGE TYPE</b>	DC
<b>DEGREE OF PROTECTION</b>	IP00 NEMA Other
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	2
<b>NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT</b>	0
<b>NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)</b>	6
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN</b>	0 V
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DUTY FACTOR</b>	100 %
<b>INTERFERENCE IMMUNITY</b>	According to EN 60947-1

<b>FUNCTIONS</b>	Reversing safety
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	24 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	24 V
<b>RATED INSULATION VOLTAGE (UI)</b>	690 V
<b>RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V</b>	25 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	25 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	25 A
<b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>	11 kW
<b>RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ</b>	3.5 kW
<b>RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ</b>	8.5 kW
<b>RATED OPERATIONAL POWER (NEMA)</b>	11 kW
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	0.9 W
<b>SUITABLE FOR</b>	Also motors with efficiency class IE3
<b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>	14 kW
<b>ACTUATING VOLTAGE</b>	24 V DC
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>VOLTAGE TYPE OF OPERATING VOLTAGE</b>	AC
<b>OPERATING VOLTAGE AT AC, 50 HZ - MIN</b>	24 V
<b>OPERATING VOLTAGE AT AC, 50 HZ - MAX</b>	690 V
<b>OPERATING VOLTAGE AT</b>	24 V

<b>AC, 60 HZ - MIN</b>	
<b>OPERATING VOLTAGE AT AC, 60 HZ - MAX</b>	690 V
<b>OPERATING VOLTAGE AT DC - MIN</b>	0 V
<b>OPERATING VOLTAGE AT DC - MAX</b>	0 V

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

