



## Eaton 111616

Eaton Moeller series xPole - PKP62/M2  
RCBO - residual-current circuit breaker with  
overcurrent protection. PKP62, 2 pole, C, In:  
13 A, 6 kA, IΔN: 0.03 A, AC current sensitive

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xPole - PKP62/M2 RCBO - residual-current circuit breaker with overcurrent protection
<b>CATALOG NUMBER</b>	111616
<b>PRODUCT LENGTH/DEPTH</b>	86 mm
<b>PRODUCT HEIGHT</b>	75 mm
<b>PRODUCT WIDTH</b>	37 mm
<b>PRODUCT WEIGHT</b>	0.25 kg
<b>COMPLIANCES</b>	CE Marked RoHS conform
<b>CERTIFICATIONS</b>	CE



Powering Business Worldwide

## □□□□

**VOLTAGE RATING** 230 V

**SURGE CURRENT CAPACITY** 0.25 kA

**VOLTAGE TYPE** AC

**WIDTH IN NUMBER OF MODULAR SPACINGS** 2

### 10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

### 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

### 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

### 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

### 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

### 10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

## □□

**CHARACTERISTIC CURVE** [eaton-xeffect-frbm6m-characteristic-curve-003.jpg](#)

[eaton-xpole-afdd-characteristic-curve-002.jpg](#)

### □□□□

[eaton-xpole-pkpm2-rcbo-catalog-ca019053en-en-us.pdf](#)

[eaton-xpole-pkp62-rcbo-catalog-ca019054en-en-us.pdf](#)

### □□

[eaton-xeffect-frbm6m-wiring-diagram-003.jpg](#)

[eaton-xeffect-frbm6m-dimensions-002.jpg](#)

[eaton-pkp-3d-drawing-002.jpg](#)

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>OPERATING AMBIENT TEMPERATURE - MAX</b>	40 °C
<b>OPERATING AMBIENT TEMPERATURE - MIN</b>	-25 °C
<b>PRODUCT APPLICATION</b>	Switchgear for industrial and advanced commercial applications
<b>PRODUCT RANGE</b>	PKP62
<b>RATED CURRENT</b>	13 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	13 A
<b>RATED SWITCHING CAPACITY (IEC/EN 61009)</b>	6 kA
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>	0 W
<b>TRIPPING CHARACTERISTIC</b>	C
<b>BUILT-IN DEPTH</b>	70 mm
<b>CURRENT LIMITING CLASS</b>	3
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60947-2)</b>	0 kA
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	40 °C

<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>FAULT CURRENT RATING</b>	0.03 A
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>	0 W
<b>NUMBER OF POLES (PROTECTED)</b>	2
<b>NUMBER OF POLES (TOTAL)</b>	2
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	230 V
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)</b>	0 kA
<b>RATED SWITCHING CAPACITY</b>	6 kA
<b>BASIC FUNCTION</b>	Combined RCD/MCB devices
<b>MOUNTING METHOD</b>	DIN rail
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	4 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>DEGREE OF PROTECTION</b>	IP20
<b>TRIPPING</b>	Non-delayed
<b>OVERVOLTAGE CATEGORY</b>	III
<b>POLLUTION DEGREE</b>	2
<b>IMPULSE WITHSTAND CURRENT</b>	Partly surge-proof, 250 A
<b>LEAKAGE CURRENT TYPE</b>	AC
<b>RELEASE CHARACTERISTIC</b>	C
<b>SENSITIVITY TYPE</b>	Type AC, AC current sensitive.
<b>FREQUENCY RATING</b>	50 Hz
<b>RATED INSULATION VOLTAGE (UI)</b>	250 V
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) -</b>	25 mm <sup>2</sup>

MAX	
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm <sup>2</sup>
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm <sup>2</sup>
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 61009)	6 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 61009-1)	6 kA
NUMBER OF POLES	Two-pole
DISCONNECTION CHARACTERISTIC	Undelayed
TYPE	RCBO
APPLICATION	Switchgear for residential and commercial applications

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: