



□□□□□

Eaton 111876

Eaton Moeller series Power Defense -
Molded Case Circuit Breaker. Circuit-breaker
LZM, 4 p, 125A, B1-4-A125-I

□□□□

PRODUCT NAME	Eaton Moeller series Power Defense molded case circuit-breaker
CATALOG NUMBER	111876
PRODUCT LENGTH/DEPTH	88 mm
PRODUCT HEIGHT	145 mm
PRODUCT WIDTH	120 mm
PRODUCT WEIGHT	1.324 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC VDE 0660

□□□□

AMPERAGE RATING	125 A
VOLTAGE RATING	440 V - 440 V
CIRCUIT BREAKER FRAME TYPE	LZM1
FEATURES	Protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

	eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-038.eps
CHARACTERISTIC CURVE	eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-032.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-051.eps
□□	eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps eaton-circuit-breaker-nzm-mccb-dimensions-018.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	DIN rail (top hat rail) mounting optional Built-in device fixed built-in technique Fixed
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	26.72 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0

PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	In the area of the HMI devices: IP20 (basic protection type) IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Frame clamp
CURRENT RATING OF NEUTRAL CONDUCTOR	200% of phase conductor
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	125 A (415 V AC-1, making and breaking capacity) 125 A (660-690 V AC-3, making and breaking capacity) 160 A (380/400 V AC-1, making and breaking capacity) 125 A (415 V AC-3, making and breaking capacity)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP00 (terminations, phase isolator and band terminal) IP10 (tunnel terminal)
NUMBER OF POLES	Four-pole
TERMINAL CAPACITY (COPPER STRIP)	Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 9 segments of 9 mm x 0.8 mm at box terminal
LIFESPAN, ELECTRICAL	7500 operations at 400 V AC-1 7500 operations at 415 V AC-3 10000 operations at 415 V AC-1
FUNCTIONS	System and cable protection
TYPE	Circuit breaker
SPECIAL FEATURES	Maximum back-up fuse, if the expected short-

	circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) - Rated current = rated uninterrupted current: 125 A - Set value in neutral conductor is synchronous with set value I_r of main pole.
APPLICATION	Use in unearthed supply systems at 440 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	125 A
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	1250 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	750 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 1.5 mm ² (2x) 0.75 mm ² - 2.5 mm ² (1x)
TERMINAL CAPACITY (COPPER BUSBAR)	Min. 12 mm x 5 mm direct at switch rear-side connection Max. 16 mm x 5 mm direct at switch rear-side connection M8 at rear-side screw connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	10 mm ² - 16 mm ² (1x) at box terminal 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 16 mm ² - 95 mm ² (1x) at tunnel terminal

	6 mm ² - 16 mm ² (2x) at box terminal 6 mm ² - 16 mm ² (2x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 70 mm ² (1x) at box terminal 25 mm ² (2x) direct at switch rear-side connection 25 mm ² - 70 mm ² (1x) direct at switch rear-side connection 25 mm ² (2x) at box terminal 25 mm ² - 95 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 95 mm ² (1x) at tunnel terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	1250 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	750 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	125 A
OVERLOAD CURRENT SETTING (IR) - MIN	100 A
OVERLOAD CURRENT SETTING (IR)	100 A - 125 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	30 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	25 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V,	18.5 kA

50/60 HZ	
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	53 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	53 kA
STANDARD TERMINALS	Box terminal
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	63 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	6000 V
RATED INSULATION VOLTAGE (UI)	690 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

