

Eaton 111962

Eaton Moeller series Power Defense -
Molded Case Circuit Breaker. Circuit-
breaker, 4 p, 500A, 230A, in 4th pole

| | |
|---------------------------------|--|
| | |
| PRODUCT NAME | Eaton Moeller series Power Defense molded case circuit-breaker |
| CATALOG NUMBER | 111962 |
| PRODUCT LENGTH/DEPTH | 166 mm |
| PRODUCT HEIGHT | 275 mm |
| PRODUCT WIDTH | 185 mm |
| PRODUCT WEIGHT | 7.3 kg |
| COMPLIANCES | RoHS conform |
| CERTIFICATIONS | VDE 0660 IEC IEC/EN 60947 |

| | |
|---|--|
| AMPERAGE RATING | 500 A |
| VOLTAGE RATING | 690 V - 690 V |
| CIRCUIT BREAKER FRAME TYPE | LZM3 |
| FEATURES | Protection unit Motor drive optional |
| 10.10 TEMPERATURE RISE | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 SHORT-CIRCUIT RATING | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 ELECTROMAGNETIC COMPATIBILITY | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 MECHANICAL FUNCTION | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |
| 10.2.2 CORROSION RESISTANCE | Meets the product standard's requirements. |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES | Meets the product standard's requirements. |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT | Meets the product standard's requirements. |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements. |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION | Meets the product standard's requirements. |
| 10.2.5 LIFTING | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 MECHANICAL IMPACT | Does not apply, since the entire switchgear needs to |

| | |
|-----------------------------|---|
| CHARACTERISTIC CURVE | eaton-circuit-breaker-nzm-mccb-characteristic-curve-035.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-032.eps eaton-circuit-breaker-tripping-characteristic-nzm-mccb-characteristic-curve.eps |
| | eaton-circuit-breaker-nzm-mccb-dimensions-021.eps eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps eaton-circuit-breaker-cable-nzm-mccb-3d-drawing-003.eps |

| | |
|---|--|
| | be evaluated. |
| 10.2.7 INSCRIPTIONS | Meets the product standard's requirements. |
| 10.3 DEGREE OF PROTECTION OF ASSEMBLIES | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 CLEARANCES AND CREEPAGE DISTANCES | Meets the product standard's requirements. |
| 10.5 PROTECTION AGAINST ELECTRIC SHOCK | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS | Is the panel builder's responsibility. |
| 10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS | Is the panel builder's responsibility. |
| 10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH | Is the panel builder's responsibility. |
| 10.9.3 IMPULSE WITHSTAND VOLTAGE | Is the panel builder's responsibility. |
| 10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL | Is the panel builder's responsibility. |
| POLLUTION DEGREE | 3 |
| MOUNTING METHOD | Built-in device fixed built-in technique Fixed |
| CLIMATIC PROOFING | Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30 |
| EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT | 130.5 W |
| UTILIZATION CATEGORY | A (IEC/EN 60947-2) |
| ISOLATION | 300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts) |
| NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS) | 0 |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY | 0 |

| | |
|--|---|
| CLOSED CONTACTS) | |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS) | 0 |
| PROTECTION AGAINST DIRECT CONTACT | Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110 |
| DEGREE OF PROTECTION | In the area of the HMI devices: IP20 (basic protection type) IP20 |
| DIRECTION OF INCOMING SUPPLY | As required |
| ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT | Screw connection |
| CURRENT RATING OF NEUTRAL CONDUCTOR | 60% of phase conductor |
| LIFESPAN, MECHANICAL | 15000 operations |
| OVERVOLTAGE CATEGORY | III |
| RATED OPERATIONAL CURRENT | 500 A (380/400 V AC-1, making and breaking capacity) 500 A (690 V AC -1, making and breaking capacity) 450 A (660-690 V AC-3, making and breaking capacity) 500 A (415 V AC-1, making and breaking capacity) 450 A (415 V AC-3, making and breaking capacity) |
| DEGREE OF PROTECTION (IP), FRONT SIDE | IP40 (with insulating surround) IP66 (with door coupling rotary handle) |
| DEGREE OF PROTECTION (TERMINATIONS) | IP10 (tunnel terminal) IP00 (terminations, phase isolator and band terminal) |
| NUMBER OF POLES | Four-pole |
| LIFESPAN, ELECTRICAL | 3000 operations at 690 V AC-1 2000 operations at 690 V AC-3 5000 operations at 400 V AC-1 2000 operations at 400 V AC-3 |
| FUNCTIONS | System and cable |

| | |
|--|---|
| | protection |
| TYPE | Circuit breaker |
| SPECIAL FEATURES | <ul style="list-style-type: none"> • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 500 A • Reduced neutral conductor protection • Set value in neutral conductor is synchronous with set value I_r of main pole. |
| APPLICATION | Use in unearthed supply systems at 690 V |
| SHOCK RESISTANCE | 20 g (half-sinusoidal shock 20 ms) |
| POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT | Front side |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 500 A |
| RELEASE SYSTEM | Thermomagnetic release |
| SHORT-CIRCUIT TOTAL BREAKTIME | < 10 ms |
| RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S) | 3.3 kA |
| RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S) | 3.3 kA |
| SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX | 5000 A |
| SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - | 3000 A |

| | |
|--|--|
| MIN | |
| TERMINAL CAPACITY (COPPER BUSBAR) | M10 at rear-side screw connection |
| TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE) | 16 mm ² - 185 mm ² (1x) at tunnel terminal |
| HANDLE TYPE | Rocker lever |
| SHORT DELAY CURRENT SETTING (ISD) - MAX | 0 A |
| SHORT DELAY CURRENT SETTING (ISD) - MIN | 0 A |
| INSTANTANEOUS CURRENT SETTING (II) - MAX | 5000 A |
| INSTANTANEOUS CURRENT SETTING (II) - MIN | 3000 A |
| NUMBER OF OPERATIONS PER HOUR - MAX | 60 |
| OVERLOAD CURRENT SETTING (IR) - MAX | 500 A |
| OVERLOAD CURRENT SETTING (IR) - MIN | 400 A |
| OVERLOAD CURRENT SETTING (IR) | 250 A - 320 A |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ | 55 kA |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ | 36 kA |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ | 22.5 kA |
| RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ | 9 kA |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ | 76 kA |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ | 63 kA |
| RATED SHORT-CIRCUIT | 24 kA |

| | |
|---|----------------|
| MAKING CAPACITY ICM AT 525 V, 50/60 HZ | |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ | 14 kA |
| STANDARD TERMINALS | Screw terminal |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ | 121 kA |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS | 6000 V |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS | 8000 V |
| VOLTAGE RATING (DC) | 750 VDC |
| RATED INSULATION VOLTAGE (UI) | 1000 V AC |

| |
|------------------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

