

Eaton 111968

Eaton Moeller series Power Defense -
Molded Case Circuit Breaker. Circuit-
breaker, 3 p, 500A, N, 3

PRODUCT NAME	Eaton Moeller series Power Defense molded case circuit-breaker
CATALOG NUMBER	111968
PRODUCT LENGTH/DEPTH	166 mm
PRODUCT HEIGHT	275 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	5.8 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 VDE 0660 IEC

AMPERAGE RATING	500 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	LZM3
FEATURES	Motor drive optional Protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to

CHARACTERISTIC CURVE	eaton-circuit-breaker-tripping-characteristic-nzm-mccb-characteristic-curve.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-031.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-034.eps
DECLARATIONS OF CONFORMITY	DA-DC-03 N3 eaton-circuit-breaker-nzm-mccb-dimensions-020.eps eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps eaton-circuit-breaker-switch-nzm-mccb-3d-drawing-002.eps

	be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Built-in device fixed built-in technique Fixed
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	93 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY	0

CLOSED CONTACTS)	
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	In the area of the HMI devices: IP20 (basic protection type) IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	15000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	500 A (500 V DC-1, making and breaking capacity) 500 A (750 V DC-3, making and breaking capacity) 500 A (750 V DC-1, making and breaking capacity) 630 A (380/400 V AC-1, making and breaking capacity) 500 A (500 V DC-3, making and breaking capacity) 630 A (690 V AC-1, making and breaking capacity) 450 A (415 V AC-3, making and breaking capacity) 450 A (660-690 V AC-3, making and breaking capacity) 500 A (415 V AC-1, making and breaking capacity)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
DEGREE OF PROTECTION (TERMINATIONS)	IP00 (terminations, phase isolator and band terminal) IP10 (tunnel terminal)
NUMBER OF POLES	Three-pole
LIFESPAN, ELECTRICAL	2000 operations at 415 V AC-3 2000 operations at 750 V DC-3

	5000 operations at 400 V AC-1 5000 operations at 415 V AC-1 5000 operations at 500 V DC-1 2000 operations at 400 V AC-3 2000 operations at 500 V DC-3 2000 operations at 690 V AC-3 3000 operations at 690 V AC-1 5000 operations at 750 V DC-1
FUNCTIONS	Photovoltaic applications System and cable protection
TYPE	Circuit breaker
SPECIAL FEATURES	<ul style="list-style-type: none"> • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 500 A
APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	500 A
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T	3.3 kA

= 0.3 S)	
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	3.3 kA
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	5000 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	3000 A
TERMINAL CAPACITY (COPPER BUSBAR)	M10 at rear-side screw connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	16 mm ² - 185 mm ² (1x) at tunnel terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	5000 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	3000 A
NUMBER OF OPERATIONS PER HOUR - MAX	60
OVERLOAD CURRENT SETTING (IR) - MAX	500 A
OVERLOAD CURRENT SETTING (IR) - MIN	400 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	85 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	50 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	35 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	13 kA

RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	105 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	74 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	53 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
STANDARD TERMINALS	Screw terminal
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	187 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	1000 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

