



□□□□□

## Eaton 112430

Eaton Moeller® series DILM Contactor, 3 pole, 380 V 400 V 18.5 kW, 1 N/O, 400 V 50 Hz, 440 V 60 Hz, AC operation, Screw terminals

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series DILM contactor
<b>CATALOG NUMBER</b>	112430
<b>PRODUCT LENGTH/DEPTH</b>	97 mm
<b>PRODUCT HEIGHT</b>	85 mm
<b>PRODUCT WIDTH</b>	45 mm
<b>PRODUCT WEIGHT</b>	0.428 kg
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	IEC 60947-4-1 UL 508 CSA Std. C22.2 No. 14-05 EN 60947-4-1 VDE VDE 0660 IEC/EN 60947 CSA UL
<b>CATALOG NOTES</b>	Contacts according to EN 50012

**ELECTRICAL  
CONNECTION TYPE FOR  
AUXILIARY- AND  
CONTROL-CURRENT  
CIRCUIT**

Screw connection

**AMPERAGE RATING**

38A

**NUMBER OF POLES**

Three-pole

**VOLTAGE RATING**

400-440 V

**10.10 TEMPERATURE RISE**

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**10.11 SHORT-CIRCUIT  
RATING**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.12 ELECTROMAGNETIC  
COMPATIBILITY**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.13 MECHANICAL  
FUNCTION**

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

**10.2.2 CORROSION  
RESISTANCE**

Meets the product standard's requirements.

**10.2.3.1 VERIFICATION OF  
THERMAL STABILITY OF  
ENCLOSURES**

Meets the product standard's requirements.

**10.2.3.2 VERIFICATION OF  
RESISTANCE OF  
INSULATING MATERIALS  
TO NORMAL HEAT**

Meets the product standard's requirements.

**10.2.3.3 RESIST. OF  
INSUL. MAT. TO  
ABNORMAL HEAT/FIRE  
BY INTERNAL ELECT.  
EFFECTS**

Meets the product standard's requirements.

**10.2.4 RESISTANCE TO  
ULTRA-VIOLET (UV)  
RADIATION**

Meets the product standard's requirements.

**10.2.5 LIFTING**

Does not apply, since the entire switchgear needs to be evaluated.

**10.2.6 MECHANICAL  
IMPACT**

Does not apply, since the entire switchgear needs to be evaluated.

## CHARACTERISTIC CURVE

[eaton-contactors-switch-dilm-characteristic-curve.eps](#)

[eaton-contactors-switch-dilm-characteristic-curve-002.eps](#)

DECLARATIONS OF  
CONFORMITY

[eaton-contactor-declaration-of-conformity-uk251218en.pdf](#)

## □□□□□

[IL03407014Z2021\\_09.pdf](#)

## □□□

[eaton-contactors-contact-dilm-wiring-diagram.eps](#)

## □□

[eaton-contactors-dimensions-210t014.eps](#)

<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FREQUENCY RATING</b>	50-60 Hz
<b>OPERATING FREQUENCY</b>	5000 mechanical Operations/h (AC operated)
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	8000 V AC
<b>UTILIZATION CATEGORY</b>	AC-3: Normal AC induction motors: starting, switch off during running AC-4: Normal AC induction motors: starting, plugging, reversing, inching AC-1: Non-inductive or slightly inductive loads, resistance furnaces
<b>CONNECTION</b>	Screw terminals
<b>FRAME SIZE</b>	FS2
<b>AMBIENT OPERATING</b>	60 °C

<b>TEMPERATURE - MAX</b>	
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	80 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)</b>	90 A
<b>CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)</b>	36 A
<b>CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)</b>	42 A
<b>CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)</b>	100 A
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	9.3 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	3.1 W
<b>APPLICATION</b>	Contactors for Motors
<b>PRODUCT CATEGORY</b>	Contactors
<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
<b>ARCING TIME</b>	10 ms
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>SCREWDRIVER SIZE</b>	0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
<b>VOLTAGE TYPE</b>	AC

<b>DEGREE OF PROTECTION</b>	IP00
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT</b>	0
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)</b>	3
<b>OPERATING TEMPERATURE - MAX</b>	60 °C
<b>OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>RATED BREAKING CAPACITY AT 220/230 V</b>	320 A
<b>RATED BREAKING CAPACITY AT 380/400 V</b>	320 A
<b>RATED BREAKING CAPACITY AT 500 V</b>	320 A
<b>RATED BREAKING CAPACITY AT 660/690 V</b>	180 A
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX</b>	400 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN</b>	400 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX</b>	440 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN</b>	440 V
<b>CONTACT CONFIGURATION</b>	1 NO
<b>DROP-OUT VOLTAGE</b>	AC operated: 0.6 - 0.3 x UC, AC operated
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DUTY FACTOR</b>	100 %
<b>EMITTED INTERFERENCE</b>	According to EN 60947-1
<b>INTERFERENCE IMMUNITY</b>	According to EN 60947-1
<b>LIFESPAN, MECHANICAL</b>	10,000,000 Operations (AC

	operated)
<b>PICK-UP VOLTAGE</b>	0.8 - 1.1 V AC x U <sub>c</sub>
<b>POWER CONSUMPTION, PICK-UP, 50 HZ</b>	52 VA, Dual-frequency coil in a cold state and 1.0 x U <sub>s</sub> , at 50 Hz
<b>SAFE ISOLATION</b>	440 V AC, Between the contacts, According to EN 61140 440 V AC, Between coil and contacts, According to EN 61140
<b>POWER CONSUMPTION, PICK-UP, 60 HZ</b>	67 VA, Dual-frequency coil in a cold state and 1.0 x U <sub>s</sub> , at 60 Hz
<b>SCREW SIZE</b>	M3.5, Terminal screw, Control circuit cables M5, Terminal screw, Main cables
<b>POWER CONSUMPTION, SEALING, 50 HZ</b>	7.1 VA, Dual-frequency coil in a cold state and 1.0 x U <sub>s</sub> , at 50 Hz 2.1 W, Dual-frequency coil in a cold state and 1.0 x U <sub>s</sub> , at 50 Hz
<b>POWER CONSUMPTION, SEALING, 60 HZ</b>	8.7 VA, Dual-frequency coil in a cold state and 1.0 x U <sub>s</sub> , at 60 Hz 2.1 W, Dual-frequency coil in a cold state and 1.0 x U <sub>s</sub> , at 60 Hz
<b>TERMINAL CAPACITY (STRANDED)</b>	1 x 16 mm <sup>2</sup> , Main cables
<b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)</b>	1 x (0.75 - 2.5) mm <sup>2</sup> , Control circuit cables 1 x (0.75 - 16) mm <sup>2</sup> , Main cables 2 x (0.75 - 2.5) mm <sup>2</sup> , Control circuit cables 2 x (0.75 - 10) mm <sup>2</sup> , Main cables
<b>SHOCK RESISTANCE</b>	6.9 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 3.5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 10 g, N/O main contact,

	<p>Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms</p> <p>7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms</p> <p>5.3 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms</p>
<b>TERMINAL CAPACITY (SOLID)</b>	<p>1 x (0.75 - 4) mm<sup>2</sup>, Control circuit cables</p> <p>2 x (0.75 - 10) mm<sup>2</sup>, Main cables</p> <p>1 x (0.75 - 16) mm<sup>2</sup>, Main cables</p> <p>2 x (0.75 - 2.5) mm<sup>2</sup>, Control circuit cables</p>
<b>TERMINAL CAPACITY (SOLID/STRANDED AWG)</b>	<p>18 - 14, Control circuit cables</p> <p>Single 18 - 6, double 18 - 8, Main cables</p>
<b>TIGHTENING TORQUE</b>	<p>3.2 Nm, Screw terminals, Main cables</p> <p>1.2 Nm, Screw terminals, Control circuit cables</p>
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	0 V
<b>RATED INSULATION VOLTAGE (UI)</b>	690 V
<b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947)</b>	384 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V</b>	45 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>	38 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	38 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V</b>	38 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3,</b>	38 A

<b>500 V</b>	
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>	22.5 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V</b>	15 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V</b>	15 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V</b>	15 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V</b>	15 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V</b>	12 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V</b>	40 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	38 A
<b>RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ</b>	12 kW
<b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>	18.5 kW
<b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>	20 kW
<b>RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ</b>	4 kW
<b>RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ</b>	4.5 kW
<b>RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ</b>	7 kW
<b>RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ</b>	7.5 kW



<b>RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ</b>	8 kW
<b>RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ</b>	9 kW
<b>RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ</b>	10 kW
<b>RATED OPERATIONAL POWER (NEMA)</b>	14.9 kW
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	690 V
<b>RESISTANCE PER POLE</b>	2.7 mΩ
<b>STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS</b>	2.1 W
<b>STRIPPING LENGTH (CONTROL CIRCUIT CABLE)</b>	10 mm
<b>STRIPPING LENGTH (MAIN CABLE)</b>	10 mm
<b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX</b>	22 ms
<b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN</b>	16 ms
<b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX</b>	14 ms
<b>SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN</b>	8 ms
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V</b>	125 A gG/gL
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V</b>	63 A gG/gL
<b>SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V</b>	63 A gG/gL
<b>SHORT-CIRCUIT</b>	35 A gG/gL

<b>PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V</b>	
<b>OPERATING TEMPERATURE</b>	-25° to 60°C
<b>CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN)</b>	45 A
<b>CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)</b>	43 A
<b>CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)</b>	40 A
<b>RATED OPERATIONAL POWER AT AC-3, 440 V, 50 HZ</b>	21 kW
<b>RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ</b>	24 kW
<b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>	21 kW
<b>ACTUATING VOLTAGE</b>	400 V 50 Hz, 440 V 60 Hz
<b>ALTITUDE</b>	Max. 2000 m
<b>OPERATING VOLTAGE AT AC, 50 HZ - MIN</b>	24 V
<b>OPERATING VOLTAGE AT AC, 50 HZ - MAX</b>	690 V
<b>OPERATING VOLTAGE AT AC, 60 HZ - MIN</b>	24 V
<b>OPERATING VOLTAGE AT AC, 60 HZ - MAX</b>	690 V

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
□□: