



00000

Eaton 109666

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 400A, A400

0000

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
CATALOG NUMBER	109666
PRODUCT LENGTH/DEPTH	166 mm
PRODUCT HEIGHT	275 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	5.8 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC IEC/EN 60947

□□□□

AMPERAGE RATING	400 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM3
FEATURES	Motor drive optional Protection unit

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

□□

CHARACTERISTIC CURVE

[eaton-circuit-breaker-tripping-characteristic-nzm-mccb-characteristic-curve.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-035.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-032.eps](#)

□□□□□

[eaton-circuit-breaker-basic-device-nzmn-blil01208009z.pdf](#)

□□

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-020.eps](#)

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
LIFESPAN, MECHANICAL	15000 operations
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
MOUNTING METHOD	Fixed Built-in device fixed built-in technique
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	72.48 W
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
NUMBER OF AUXILIARY	0

CONTACTS (CHANGE-OVER CONTACTS)**NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)**

0

NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)

0

PROTECTION AGAINST DIRECT CONTACT

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110

DEGREE OF PROTECTIONIP20 (basic degree of protection, in the operating controls area)
IP20**DIRECTION OF INCOMING SUPPLY**

As required

ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT

Screw connection

OVERVOLTAGE CATEGORY

III

DEGREE OF PROTECTION (IP), FRONT SIDEIP66 (with door coupling rotary handle)
IP40 (with insulating surround)**DEGREE OF PROTECTION (TERMINATIONS)**IP00 (terminations, phase isolator and strip terminal)
IP10 (tunnel terminal)**NUMBER OF POLES**

Three-pole

10 segments of 50 mm x 1 mm (2x) at rear-side width extension
Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)**TERMINAL CAPACITY (COPPER STRIP)**Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)
Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm
Max. 8 segments of 24 mm x 1 mm (2x) at box terminal
Min. 6 segments of 16 mm x 0.8 mm at box terminal**LIFESPAN, ELECTRICAL**5000 operations at 400 V
AC-1
3000 operations at 690 V
AC-1
2000 operations at 690 V

AC-3 5000 operations at 415 V AC-1 2000 operations at 415 V AC-3 2000 operations at 400 V AC-3	
FUNCTIONS	System and cable protection
TYPE	Circuit breaker
SPECIAL FEATURES	<ul style="list-style-type: none"> • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 400 A • Terminal capacity hint: Up to 240 mm² can be connected depending on the cable manufacturer.
APPLICATION	Use in unearthing supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	400 A
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	3.3 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	3.3 kA
SHORT-CIRCUIT RELEASE	4000 A

NON-DELAYED SETTING -**MAX****SHORT-CIRCUIT RELEASE****NON-DELAYED SETTING -**

2400 A

MIN**TERMINAL CAPACITY
(CONTROL CABLE)**0.75 mm² - 1.5 mm² (2x)
0.75 mm² - 2.5 mm² (1x)Min. 20 mm x 5 mm direct
at switch rear-side
connectionMax. 10 mm x 50 mm (2x)
at rear-side width
extension**TERMINAL CAPACITY
(COPPER BUSBAR)**M10 at rear-side screw
connectionMax. 30 mm x 10 mm + 30
mm x 5 mm direct at
switch rear-side
connection**TERMINAL CAPACITY
(COPPER SOLID
CONDUCTOR/CABLE)**16 mm² (2x) at box
terminal16 mm² (2x) direct at
switch rear-side
connection16 mm² (1x) at tunnel
terminal300 mm² (2x) at rear-side
width extension16 mm² (1x) direct at
switch rear-side
connection**TERMINAL CAPACITY
(ALUMINUM SOLID
CONDUCTOR/CABLE)**16 mm² (1x) at tunnel
terminal35 mm² - 240 mm² (1x) at
box terminal16 mm² - 185 mm² (1x) at
1-hole tunnel terminal**TERMINAL CAPACITY
(COPPER STRANDED
CONDUCTOR/CABLE)**25 mm² - 120 mm² (2x) at
box terminal25 mm² - 240 mm² (1x)
direct at switch rear-side
connection25 mm² - 240 mm² (2x)
direct at switch rear-side
connection**TERMINAL CAPACITY
(ALUMINUM STRANDED
CONDUCTOR/CABLE)**50 mm² - 240 mm² (2x) at
2-hole tunnel terminal50 mm² - 240 mm² (1x) at
2-hole tunnel terminal25 mm² - 185 mm² (1x) at
tunnel terminal**HANDLE TYPE**

Rocker lever

INSTANTANEOUS**CURRENT SETTING (II) -**

4000 A

MAX

INSTANTANEOUS	
CURRENT SETTING (II) -	2400 A
MIN	
NUMBER OF	
OPERATIONS PER HOUR -	60
MAX	
OVERLOAD CURRENT	
SETTING (IR) - MAX	400 A
OVERLOAD CURRENT	
SETTING (IR) - MIN	320 A
RATED SHORT-CIRCUIT	
BREAKING CAPACITY ICS	
(IEC/EN 60947) AT 230 V,	55 kA
50/60 Hz	
RATED SHORT-CIRCUIT	
BREAKING CAPACITY ICS	
(IEC/EN 60947) AT	36 kA
400/415 V, 50/60 Hz	
RATED SHORT-CIRCUIT	
BREAKING CAPACITY ICS	
(IEC/EN 60947) AT 440 V,	22.5 kA
50/60 Hz	
RATED SHORT-CIRCUIT	
BREAKING CAPACITY ICS	
(IEC/EN 60947) AT 525 V,	9 kA
50/60 Hz	
RATED SHORT-CIRCUIT	
BREAKING CAPACITY ICS	
(IEC/EN 60947) AT 690 V,	4 kA
50/60 Hz	
RATED SHORT-CIRCUIT	
MAKING CAPACITY ICM	76 kA
AT 400/415 V, 50/60 Hz	
RATED SHORT-CIRCUIT	
MAKING CAPACITY ICM	63 kA
AT 440 V, 50/60 Hz	
RATED SHORT-CIRCUIT	
MAKING CAPACITY ICM	24 kA
AT 525 V, 50/60 Hz	
RATED SHORT-CIRCUIT	
MAKING CAPACITY ICM	14 kA
AT 690 V, 50/60 Hz	
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection on rear. Tunnel terminal
RATED SHORT-CIRCUIT	
MAKING CAPACITY ICM	121 kA
AT 240 V, 50/60 Hz	
RATED IMPULSE	
WITHSTAND VOLTAGE	
(UIMP) AT AUXILIARY	6000 V
CONTACTS	
RATED IMPULSE	8000 V

WITHSTAND VOLTAGE**(UIMP) AT MAIN****CONTACTS****RATED INSULATION****VOLTAGE (UI)**

1000 V AC

□□□□:

□□□□:

□□□:

□□:

*Powering Business Worldwide*

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

□□□□□□□□□□□□□□□□□□□□□□□□

