



□□□□□

Eaton 112749

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 50A, plug-in module, C1-S50-SVE

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker magnetic
CATALOG NUMBER	112749
PRODUCT LENGTH/DEPTH	90 mm
PRODUCT HEIGHT	201 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	1.227 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC

□□□□	
AMPERAGE RATING	50 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM1
ACCESSORIES REQUIRED	NZM1-XSVS
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□	
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-058.eps
	eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-039.eps
	eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-033.eps
	eaton-circuit-breaker-nzm-mccb-characteristic-curve-033.eps
□□□□□	eaton-circuit-breaker-switch-disconnector-nzmb-il01203004z.pdf
□□	eaton-circuit-breaker-nzm-mccb-dimensions-017.eps
	eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps
	eaton-circuit-breaker-adapter-nzm-mccb-dimensions.eps
	eaton-circuit-breaker-socket-nzm-mccb-3d-drawing.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Plug-in unit Built-in device plug-in technique
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	13.2 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to VDE 0106 part 100

RATED INSULATION VOLTAGE (UI)	690 V
RATED OPERATING POWER AT AC-3, 230 V	15 kW
RATED OPERATING POWER AT AC-3, 400 V	22 kW
SWITCH OFF TECHNIQUE	Magnetic
DEGREE OF PROTECTION	IP20 IP20 (basic degree of protection, in the operating controls area)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Other
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	41 A (400 V AC-3)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 9 segments of 9 mm x 0.8 mm at box terminal
LIFESPAN, ELECTRICAL	7500 operations at 415 V AC-1 5000 operations at 690 V AC-1 10000 operations at 400 V AC-1
FUNCTIONS	Short-circuit protection
TYPE	Circuit breaker
SPECIAL FEATURES	Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit

	breaking capacity Icn) • Motor protection in conjunction with overload relay • With short-circuit release • Without overload release Ir • IEC/EN 60947-4-1, IEC/EN 60947-2 • The circuit-breaker fulfills all requirements for AC-3 switching category. • Rated current = rated uninterrupted current: 50 A • Terminal capacity hint: Up to 95 mm² can be connected depending on the cable manufacturer.
--	---

APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	50 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	700 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	400 A
HANDLE TYPE	Rocker lever
INSTANTANEOUS CURRENT SETTING (II) - MAX	14 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	8 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	0 A
OVERLOAD CURRENT SETTING (IR) - MIN	0 A

RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	55 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	22.5 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	22.5 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	6 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	4 kA
STANDARD TERMINALS	Box terminal
OPTIONAL TERMINALS	Connection on rear. Screw terminal. Tunnel terminal
RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 10 mm ² - 16 mm ² (2x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 95 mm ² (1x) at tunnel terminal 25 mm ² - 35 mm ² (1x) direct at switch rear-side connection 25 mm ² - 35 mm ² (2x) direct at switch rear-side connection
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 2.5 mm ² (1x) 0.75 mm ² - 1.5 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 16 mm x 5 mm direct at switch rear-side connection M6 at rear-side screw connection Min. 12 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID)	10 mm ² - 16 mm ² (1x) at box terminal

CONDUCTOR/CABLE)	6 mm ² - 16 mm ² (2x) at box terminal 10 mm ² - 16 mm ² (1x) direct at switch rear-side connection 6 mm ² - 16 mm ² (2x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	10 mm ² - 70 mm ² (1x) direct at switch rear-side connection 10 mm ² - 70 mm ² (1x) at box terminal 25 mm ² (2x) direct at switch rear-side connection 6 mm ² - 25 mm ² (2x) at box terminal 25 mm ² - 95 mm ² (1x) at 1-hole tunnel terminal
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ	22.5 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	76 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	63 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	24 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	14 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	121 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	6000 V
POWER LOSS	4.2 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

