

Eaton 113415

Eaton Moeller series Circuit breaker NZMS3,
Electronic, Four-pole, 630 A, 690 V, AE, Screw
connection

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker electronic
CATALOG NUMBER	113415
PRODUCT LENGTH/DEPTH	166 mm
PRODUCT HEIGHT	275 mm
PRODUCT WIDTH	185 mm
PRODUCT WEIGHT	8.425 kg
COMPLIANCES	RoHS conform

AMPERAGE RATING	630 A
VOLTAGE RATING	690 V - 690 V
FEATURES	Motor drive optional Protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product

	standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Built-in device fixed built-in technique
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
DEGREE OF PROTECTION	IP20
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Four-pole
FUNCTIONS	Integrated earth fault protection
TYPE	Circuit breaker
POSITION OF	Front side

CONNECTION FOR MAIN CURRENT CIRCUIT	
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	5040 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	1260 A
OVERLOAD CURRENT SETTING (IR) - MAX	630 A
OVERLOAD CURRENT SETTING (IR) - MIN	315 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	100 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	70 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	65 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	18 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	6 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 525 V, 50/60 HZ	36 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ	70 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 230 V, 50/60 HZ	100 kA
RATED SHORT-CIRCUIT	25 kA

**BREAKING CAPACITY ICU
(IEC/EN 60947) AT 690 V,
50/60 HZ**

**RATED SHORT-CIRCUIT
BREAKING CAPACITY ICU
(IEC/EN 60947) AT 440 V,
50/60 HZ** 65 kA

**RATED SHORT-CIRCUIT
BREAKING CAPACITY ICU
(UL489, CSA22.2) AT 240
V, 60 HZ** 100 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

