



□□□□□

Eaton 113537

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 4p, 500A, 320A in 4th pole, withdrawable unit, NZMN3-4-A500/320-AVE

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
CATALOG NUMBER	113537
PRODUCT LENGTH/DEPTH	346 mm
PRODUCT HEIGHT	260 mm
PRODUCT WIDTH	230 mm
PRODUCT WEIGHT	12.9 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC IEC/EN 60947

□□□□

AMPERAGE RATING	500 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM3
FEATURES	Protection unit Motor drive optional
ACCESSORIES REQUIRED	NZM3-4-XAVS
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.

□□

	eaton-circuit-breaker-tripping-characteristic-nzm-mccb-characteristic-curve.eps
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-031.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-034.eps
□□□□□	eaton-circuit-breaker-basic-device-nzmn-b-il01208009z.pdf
	eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps
□□	eaton-circuit-breaker-withdrawable-unit-nzm-mccb-dimensions-002.eps eaton-circuit-breaker-nzm-mccb-dimensions-021.eps

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Built-in device slide-in technique (withdrawable) Withdrawable
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	130.5 W
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C

NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 (basic degree of protection, in the operating controls area) IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
CURRENT RATING OF NEUTRAL CONDUCTOR	320 A 60% of phase conductor
LIFESPAN, MECHANICAL	15000 operations
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Four-pole
TERMINAL CAPACITY (COPPER STRIP)	Min. 6 segments of 16 mm x 0.8 mm at box terminal Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched) Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched) Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm Max. 8 segments of 24 mm x 1 mm (2x) at box terminal 10 segments of 50 mm x 1 mm (2x) at rear-side width extension
LIFESPAN, ELECTRICAL	2000 operations at 690 V

	AC-3 2000 operations at 415 V AC-3 2000 operations at 400 V AC-3 3000 operations at 690 V AC-1 5000 operations at 415 V AC-1 5000 operations at 400 V AC-1
FUNCTIONS	System and cable protection
TYPE	Circuit breaker
SPECIAL FEATURES	• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • Rated current = rated uninterrupted current: 500 A • Reduced neutral conductor protection • Set value in neutral conductor is synchronous with set value I_r of main pole. • Terminal capacity hint: Up to 240 mm² can be connected depending on the cable manufacturer.
APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	500 A

RELEASE SYSTEM	Thermomagnetic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	3.3 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	3.3 kA
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	5000 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	3000 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 2.5 mm ² (1x) 0.75 mm ² - 1.5 mm ² (2x)
TERMINAL CAPACITY (COPPER BUSBAR)	M10 at rear-side screw connection Min. 20 mm x 5 mm direct at switch rear-side connection Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection Max. 10 mm x 50 mm (2x) at rear-side width extension
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal 16 mm ² (2x) at box terminal 300 mm ² (2x) at rear-side width extension 16 mm ² (2x) direct at switch rear-side connection 16 mm ² (1x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	35 mm ² - 240 mm ² (1x) at box terminal 25 mm ² - 240 mm ² (1x) direct at switch rear-side connection 25 mm ² - 120 mm ² (2x) at box terminal 16 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal 25 mm ² - 240 mm ² (2x) direct at switch rear-side connection

TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 185 mm ² (1x) at tunnel terminal 50 mm ² - 240 mm ² (2x) at 2-hole tunnel terminal 50 mm ² - 240 mm ² (1x) at 2-hole tunnel terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	10 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	6 A
NUMBER OF OPERATIONS PER HOUR - MAX	60
OVERLOAD CURRENT SETTING (IR) - MAX	500 A
OVERLOAD CURRENT SETTING (IR) - MIN	400 A
OVERLOAD CURRENT SETTING (IR)	250 A - 320 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	85 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	50 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	35 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	13 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	5 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	105 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	74 kA
RATED SHORT-CIRCUIT	53 kA

MAKING CAPACITY ICM AT 525 V, 50/60 HZ	
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection on rear. Tunnel terminal
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	187 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	1000 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

