



□□□□□

## Eaton 112003

Eaton Moeller series Power Defense -  
Molded Case Circuit Breaker. Switch-  
disconnecter, 3 p, 200A, frame size 2

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series Power Defense molded case switch-disconnector
<b>CATALOG NUMBER</b>	112003
<b>PRODUCT LENGTH/DEPTH</b>	142 mm
<b>PRODUCT HEIGHT</b>	185 mm
<b>PRODUCT WIDTH</b>	105 mm
<b>PRODUCT WEIGHT</b>	2.15 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC

□□□□	
AMPERAGE RATING	200 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	LN2
FEATURES	Version as main switch Motor drive optional Version as maintenance- /service switch Version as emergency stop installation
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	Does not apply, since the

□□	
□□□□□	<a href="#">eaton-circuit-breaker-basic-unit-lzm2-il01206012z.pdf</a>
□□	<a href="#">eaton-circuit-breaker-nzm-mccb-dimensions-019.eps</a>

<b>IMPACT</b>	entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	3
<b>MOUNTING METHOD</b>	Ground mounting Distribution board installation Intermediate mounting Fixed Built-in device fixed built-in technique
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	30.72 W
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	3.5 kA
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY</b>	0

<b>CONTACTS (NORMALLY OPEN CONTACTS)</b>	
<b>RATED INSULATION VOLTAGE (UI)</b>	690 V
<b>RATED OPERATING FREQUENCY</b>	50 Hz
<b>RATED OPERATING POWER AT AC-23, 400 V</b>	110 kW
<b>RATED OPERATING POWER AT AC-3, 400 V</b>	0 kW
<b>SWITCH POSITIONS</b>	I, +, 0
<b>LIFESPAN, MECHANICAL</b>	20000 operations
<b>OVERVOLTAGE CATEGORY</b>	III
<b>RATED OPERATIONAL CURRENT</b>	250 A (690 V AC-22/23A, making and breaking capacity) 250 A (690 V AC-1, making and breaking capacity) 250 A (415 V AC-22/23A, making and breaking capacity) 250 A (415 V AC-1, making and breaking capacity)
<b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>	IP20
<b>NUMBER OF POLES</b>	Three-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	Max. 10 segments of 16 mm x 0.8 mm at box terminal Max. 10 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Min. 2 segments of 9 mm x 0.8 mm at box terminal
<b>HANDLE COLOR</b>	Gray
<b>LIFESPAN, ELECTRICAL</b>	5000 operations at 690 V AC-3 10000 operations at 415 V AC-1 7500 operations at 415 V AC-3 10000 operations at 400 V AC-1 7500 operations at 400 V AC-3 7500 operations at 690 V AC-1
<b>FUNCTIONS</b>	Disconnectors/main switches Voltage release optional

	Interlockable
<b>TYPE</b>	Switch-disconnector
<b>SPECIAL FEATURES</b>	Main switch characteristics including positive drive to IEC/EN 60204 and VDE 0113. Isolating characteristics to IEC/EN 60947-3 and VDE 0660. Busbar tag shroud to VDE 0160 Part 100. Rated current = rated uninterrupted current: 200 A
<b>APPLICATION</b>	Use in unearthed supply systems at 690 V
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	100 kA
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT WITH BACK-UP FUSE</b>	100 kA at 400/415 V PN2(N2)-160...250: 250 AgGgL 80 kA at 690 V
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT WITH DOWNSTREAM FUSE</b>	PN2(N2)-160...250: 250 AgGgL 80 kA at 690 V 100 kA at 400/415 V
<b>SHORT-CIRCUIT TOTAL BREAKTIME</b>	< 10 ms
<b>RATED OPERATING VOLTAGE (UE) AT AC - MAX</b>	400 V
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	200 A
<b>RATED PERMANENT CURRENT AT AC-21, 400 V</b>	0 A
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)</b>	3.5 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>	3.5 kA
<b>SWITCHING POWER AT 400 V</b>	0 kW
<b>HANDLE TYPE</b>	Rocker lever
<b>NUMBER OF OPERATIONS PER HOUR - MAX</b>	120
<b>RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ</b>	5.5 kA
<b>RATED IMPULSE WITHSTAND VOLTAGE</b>	6000 V

<b>(UIMP) AT AUXILIARY CONTACTS</b>	
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS</b>	8000 V
<b>STANDARD TERMINALS</b>	Screw terminal
<b>TERMINAL CAPACITY (CONTROL CABLE)</b>	0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x) 0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x)
<b>SHORT-CIRCUIT PROTECTIVE DEVICE FUSES - MAX</b>	250 A gL
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	M8 at rear-side screw connection Min. 16 mm x 5 mm direct at switch rear-side connection Max. 20 mm x 5 mm direct at switch rear-side connection
<b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>	4 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) direct at switch rear-side connection 4 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) direct at switch rear-side connection 4 mm <sup>2</sup> - 16 mm <sup>2</sup> (1x) at box terminal 4 mm <sup>2</sup> - 16 mm <sup>2</sup> (2x) at box terminal 16 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)</b>	16 mm <sup>2</sup> (1x) at tunnel terminal
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal 25 mm <sup>2</sup> - 70 mm <sup>2</sup> (2x) direct at switch rear-side connection 25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) direct at switch rear-side connection 25 mm <sup>2</sup> - 70 mm <sup>2</sup> (2x) at box terminal 25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at box terminal
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at tunnel terminal

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

