



□□□□□

Eaton 112627

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 160A, +residual current circuit-breaker, 30mA, AC/DC sensitive

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker thermo-magnetic
CATALOG NUMBER	112627
PRODUCT LENGTH/DEPTH	293 mm
PRODUCT HEIGHT	145 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	4.738 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC VDE 0660 EN 62423: Type B IEC/EN 60947



Powering Business Worldwide

□□□□

AMPERAGE RATING	160 A
VOLTAGE RATING	400 V - 400 V
CIRCUIT BREAKER FRAME TYPE	NZM2
FEATURES	Motor drive optional Protection unit
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

	eaton-circuit-breaker-let-through-current-nzm-mccb-characteristic-curve-005.eps
	eaton-circuit-breaker-characteristic-power-defense-mccb-characteristic-curve-037.eps
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-003.eps
	eaton-circuit-breaker-nzm-mccb-characteristic-curve-050.eps
□□□□□	eaton-residual-current-device-3-pole-nzm2-il01219040z.pdf
	eaton-circuit-breaker-current-nzm-mccb-dimensions.eps
	eaton-circuit-breaker-nzm-mccb-dimensions-019.eps
□□	eaton-circuit-breaker-symbol-nzm-earth-fault-release-symbol.eps
	eaton-general-nzm-mccb-symbol.eps
	eaton-circuit-breaker-nzm-mccb-3d-drawing-003.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	DIN rail (top hat rail) mounting optional Fixed Built-in device fixed built-in technique
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY	0

CONTACTS (NORMALLY CLOSED CONTACTS)	
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 (basic degree of protection, in the operating controls area) IP20
DIRECTION OF INCOMING SUPPLY	Bottom
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	20000 operations
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP40 (with insulating surround) IP66 (with door coupling rotary handle)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Min. 2 segments of 16 mm x 0.8 mm at rear-side connection (punched) Max. 10 segments of 16 mm x 0.8 mm at box terminal Min. 2 segments of 9 mm x 0.8 mm at box terminal Max. 10 segments of 24 mm x 0.8 mm at rear-side connection (punched) Max. 8 segments of 24 mm x 1 mm (2x) at box terminal
LIFESPAN, ELECTRICAL	10000 operations at 400 V AC-1 10000 operations at 415 V AC-1 6500 operations at 400 V AC-3 6500 operations at 415 V AC-3
FUNCTIONS	System and cable protection, fire protection, personnel protection
TYPE	Circuit breaker

SPECIAL FEATURES

- For equipment with power electronics, such as inverters and variable frequency drives
 - Ready-to-connect combination consisting of type B circuit-breaker and residual current circuit-breaker and type A passive section
 - Suitability for the application in three-phase systems without neutral conductor
 - Personnel protection and preventive fire protection for 0 - 100 kHz fault current frequency
 - Operational voltage range Type B 50 - 400 V AC (+ 10 %)
 - Type A functionality even without operational voltage for rated frequency of 50 Hz
 - Not UL/CSA approved
 - Adjusting buttons can be sealed.
 - Rated operating voltage 400 V AC (+/- 10 %)
 - Rated frequency 50 Hz
 - Rated fault current $I_{\Delta n} = 0.03 \text{ A}$
 - Depending on the cable manufacturer up to 240 mm² can be connected
 - Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity
-

- lcn)
- Rated current = rated uninterrupted current: 160 A

APPLICATION	Use in unearthed supply systems at 400 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	160 A
POWER LOSS	38.4 W
RELEASE SYSTEM	Thermomagnetic release, AC/DC sensitive earth-fault release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	1.9 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	1.9 kA
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	1600 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	960 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 1.5 mm ² (2x) 0.75 mm ² - 2.5 mm ² (1x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 24 mm x 8 mm direct at switch rear-side connection Min. 16 mm x 5 mm direct at switch rear-side connection M8 at rear-side screw connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	10 mm ² - 16 mm ² (1x) at box terminal 6 mm ² - 16 mm ² (2x) at box terminal 6 mm ² - 16 mm ² (2x) direct at switch rear-side connection 16 mm ² (1x) at tunnel terminal

	10 mm ² - 16 mm ² (1x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal 25 mm ² - 185 mm ² (1x) direct at switch rear-side connection 25 mm ² - 70 mm ² (2x) at box terminal 25 mm ² - 70 mm ² (2x) direct at switch rear-side connection 25 mm ² - 185 mm ² (1x) at box terminal
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 185 mm ² (1x) at tunnel terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	0 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	0 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	1600 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	960 A
NUMBER OF OPERATIONS PER HOUR - MAX	120
OVERLOAD CURRENT SETTING (IR) - MAX	160 A
OVERLOAD CURRENT SETTING (IR) - MIN	125 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	150 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	330 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection on rear. Tunnel terminal

RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	330 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	1000 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: