



## Eaton 115413

Eaton Moeller® series LS Position switch,  
Roller plunger, 1 N/O, 1 NC

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series LS Position switch
<b>CATALOG NUMBER</b>	115413
<b>PRODUCT LENGTH/DEPTH</b>	33.5 mm
<b>PRODUCT HEIGHT</b>	106 mm
<b>PRODUCT WIDTH</b>	31 mm
<b>PRODUCT WEIGHT</b>	0.079 kg
<b>COMPLIANCES</b>	CE
<b>CATALOG NOTES</b>	The operating head can be rotated 90° to enable adaptation to the specified approach direction

<b>TYPE</b>	Operating heads
<b>FEATURES</b>	Forced opening
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND</b>	Meets the product

DECLARATIONS OF CONFORMITY	<a href="#">eaton-position-switch-declaration-of-conformity-uk251032en.pdf</a>
□□□□□	<a href="#">IL053001ZU</a>
□□	<a href="#">eaton-position-switches-plunger-ls-dimensions-003.eps</a>

<b>CREEPAGE DISTANCES</b>	standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>ELECTRIC CONNECTION TYPE</b>	Cable entry metrical
<b>ENCLOSURE MATERIAL FINISHING</b>	Other
<b>ACTUATOR ALIGNMENT</b>	Roller cam straight
<b>ENCLOSURE MATERIAL</b>	Plastic
<b>ENCLOSURE TYPE</b>	Cuboid
<b>RATED OPERATIONAL CURRENT (IE) AT DC-13, 125 V</b>	0.8 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V</b>	0.3 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V</b>	3 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	6 A
<b>SENSOR HEIGHT</b>	61 mm
<b>SENSOR LENGTH</b>	33.5 mm
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	0 W
<b>WIDTH SENSOR</b>	31 mm
<b>PRODUCT CATEGORY</b>	Roller plunger
<b>ACTION</b>	2020122120328-Mechanical Limit Switches.xlsm-Data

<b>EXPLOSION SAFETY CATEGORY FOR DUST</b>	None
<b>EXPLOSION SAFETY CATEGORY FOR GAS</b>	None
<b>ACTUATOR TYPE</b>	Roller cam
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>DIAMETER SENSOR</b>	0 mm
<b>EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID</b>	0 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID</b>	0.17 W
<b>NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	1
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>NUMBER OF SAFETY AUXILIARY CONTACTS</b>	1
<b>RATED OPERATIONAL CURRENT (IE) AT AC-15, 125 V</b>	6 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V</b>	6 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-15, 24 V</b>	6 A
<b>DEGREE OF PROTECTION</b>	IP66/IP67 NEMA Other
<b>INTERFACE TYPE</b>	None
<b>SWITCH FUNCTION TYPE</b>	Slow-action switch
<b>SUITABLE FOR</b>	Safety functions

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

