



Eaton 116670

Eaton xEnergy Basic LV systems Low voltage switchgear. Surface-mount installation distribution board with rotary lever, IP55, HxWxD=1560x1000x270mm

□□□□

PRODUCT NAME	Eaton xEnergy Basic small distribution board
CATALOG NUMBER	116670
PRODUCT LENGTH/DEPTH	270 mm
PRODUCT HEIGHT	1560 mm
PRODUCT WIDTH	1000 mm
PRODUCT WEIGHT	51.8 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

TYPE	Basic device
FEATURES	EMC-version
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility.
10.13 MECHANICAL FUNCTION	Meets the product standard's requirements.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Not relevant to indoor installations.
10.2.5 LIFTING	Does not apply to enclosures without lifting aids.
10.2.6 MECHANICAL IMPACT	IK10
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	IP55
10.4 CLEARANCES AND CREEPAGE DISTANCES	Is the panel builder's responsibility.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	< 0.1 Ω; meets the product standard's requirements.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Is the panel builder's responsibility.
10.7 INTERNAL	Is the panel builder's

	bpm o 1000 15 p.stp
MCAD MODEL	eaton-empty-consumer-units-mcad-drawings-bpm-o-1000-15-p.dwg

ELECTRICAL CIRCUITS AND CONNECTIONS	responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Ui = 440 V AC
10.9.3 IMPULSE WITHSTAND VOLTAGE	4 kV
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Does not apply to metal enclosures.
SURFACE FINISHING	With powder coating
ENCLOSURE MATERIAL	Steel
BUILT-IN HEIGHT	1590 mm
BUILT-IN WIDTH	1030 mm
BUILT-IN DEPTH	300 mm
HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)	204 W
HEAT DISS. AMBIENT 35°C DELTA T: 20°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)	185 W
HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)	198 W
CLOSURE TYPE	Other
COVER/DOOR MODEL	Closed
COVER/DOOR TYPE	Door Rotary lever Double
RAL-NUMBER	7035
WIDTH IN NUMBER OF MODULAR SPACINGS	46
APPLICATION	Moisture-proof (installation site)
COLOR	Light gray (RAL 7035) Gray
NUMBER OF ROWS	9
DEGREE OF PROTECTION	IP55
FUNCTIONS	Basic device Extension possible Sealable
MATERIAL	Sheet steel
MOUNTING METHOD	Surface mounting Surface mounted (plaster)

HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)	409 W
HEAT DISS. AMBIENT 35°C DELTA T: 35°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)	370 W
HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)	398 W
INTERNAL DEPTH	265 mm
NUMBER OF OPENINGS FOR SOCKET OUTLETS	0

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

