

Eaton 118916

Eaton Moeller® series DILMP Contactor, 4 pole, 45 A, 1 NC, 24 V DC, DC operation

PRODUCT NAME	Eaton Moeller® series DILMP 4-pole contactor
CATALOG NUMBER	118916
PRODUCT LENGTH/DEPTH	97 mm
PRODUCT HEIGHT	85 mm
PRODUCT WIDTH	58 mm
PRODUCT WEIGHT	0.596 kg
CERTIFICATIONS	CSA Class No.: 2411-03, 3211-04 IEC/EN 60947-4-1 UL File No.: E29096 CSA File No.: 012528 CE IEC/EN 60947 VDE 0660 CSA UL Category Control No.: NLDX CSA-C22.2 No. 60947-4-1-14 UL UL 60947-4-1
CATALOG NOTES	Also tested according to AC-3e.

NUMBER OF POLES	Four-pole
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

IL03407049Z	

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Mirror contact Suppressor circuit in actuating electronics
OPERATING FREQUENCY	5000 mechanical Operations/h (DC operated) 5000 mechanical Operations/h (AC operated)
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-3
CONNECTION TO SMARTWIRE-DT	In conjunction with DIL-SWD SmartWire DT contactor module Yes
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	8000 V AC
UTILIZATION CATEGORY	AC-1: Non-inductive or slightly inductive loads, resistance furnaces AC-3: Normal AC induction motors: starting, switch off during running
CONNECTION	Screw terminals

AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	2 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	7.5 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	5 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	10 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	15 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	20 HP
CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)	105 A
CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)	36 A
CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)	40 A
CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1- POLE, OPEN)	117 A
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	13.2 W
HEAT DISSIPATION CAPACITY PDISS	0 W

HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	4.4 W
SWITCHING TIME (DC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX	47 ms
SWITCHING TIME (DC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX	30 ms
APPLICATION	Contactors for 4 pole electric consumers
PRODUCT CATEGORY	Contactors
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
ARCING TIME	10 ms
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
SCREWDRIVER SIZE	0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
VOLTAGE TYPE	DC
DEGREE OF PROTECTION	IP00
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT	0
NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)	4
POWER CONSUMPTION (PICK-UP) AT DC	12 W
POWER CONSUMPTION (SEALING) AT DC	0.9 W

RATED BREAKING CAPACITY AT 220/230 V	250 A
RATED BREAKING CAPACITY AT 380/400 V	250 A
RATED BREAKING CAPACITY AT 500 V	250 A
RATED BREAKING CAPACITY AT 660/690 V	144 A
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
DROP-OUT VOLTAGE	0.2 - 0.6 x UC, DC operated
OVERVOLTAGE CATEGORY	III
DUTY FACTOR	100 %
INTERFERENCE IMMUNITY	According to EN 60947-1
LIFESPAN, MECHANICAL	10,000,000 Operations (AC operated) 10,000,000 Operations (DC operated)
PICK-UP VOLTAGE	0.7 - 1.2 V DC x Uc 0.85 - 1.1 V AC/DC x Us
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140 440 V AC, Between coil and contacts, According to EN 61140
RESIDUAL CURRENT	1 mA (with actuation of A1 - A2 by the electronics with "0" signal)
SCREW SIZE	M3.5, Terminal screw, Control circuit cables M5, Terminal screw, Main cables
TERMINAL CAPACITY (STRANDED)	1 x 16 mm ² , Main cables
SWITCHING CAPACITY (AUXILIARY CONTACTS,	1 A, 250 V DC, (UL/CSA) 10 A, 600 V AC, (UL/CSA)

GENERAL USE)	
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	P300, DC operated (UL/CSA) A600, AC operated (UL/CSA)
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.75 - 1.5) mm ² 2 x (0.75 - 1.5) mm ²
SHOCK RESISTANCE	5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 16) mm ² , Main cables 2 x (0.75 - 2.5) mm ² , Control circuit cables 1 x (0.75 - 4) mm ² , Control circuit cables 2 x (0.75 - 10) mm ² , Main cables 1 x (0.75 - 2.5) mm ²
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 6, Main cables 18 - 14, Control circuit cables
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	40 A, Maximum motor rating (UL/CSA)
TIGHTENING TORQUE	1.2 Nm, Screw terminals, Control circuit cables 3 Nm, Screw terminals, Main cables
TERMINAL CAPACITY (FLEXIBLE)	1 x (0.75 - 2.5) mm ² 2 x (0.75 - 2.5) mm ²
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	27 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	24 V
RATED INSULATION VOLTAGE (UI)	690 V
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN	350 A

60947)	
RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V	45 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	25 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	25 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V	25 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	25 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	15 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V	15 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V	45 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V	45 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V	45 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	45 A
RATED OPERATIONAL POWER AT AC-1, 220/230 V, 50 HZ	16 kW
RATED OPERATIONAL POWER AT AC-1, 240 V, 50 HZ	18 kW
RATED OPERATIONAL POWER AT AC-1, 380/400 V, 50 HZ	28 kW
RATED OPERATIONAL POWER AT AC-1, 415 V, 50 HZ	31 kW
RATED OPERATIONAL POWER AT AC-1, 440 V, 50 HZ	33 kW
RATED OPERATIONAL	37 kW

POWER AT AC-1, 500 V, 50 HZ	
RATED OPERATIONAL POWER AT AC-1, 690 V, 50 HZ	49 kW
RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ	8.5 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	11 kW
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	14.5 kW
RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ	7 kW
RATED OPERATIONAL POWER (NEMA)	11 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RESISTANCE PER POLE	2.7 mΩ
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0.9 W
STRIPPING LENGTH (CONTROL CIRCUIT CABLE)	10 mm
STRIPPING LENGTH (MAIN CABLE)	10 mm
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	5 kA, SCCR (UL/CSA) 125 A, max. Fuse, SCCR (UL/CSA) 125 A, max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)	50/32 A, max. CB, SCCR (UL/CSA) 10/100 kA, Fuse, SCCR (UL/CSA) 125/70 A, Class J, max. Fuse, SCCR (UL/CSA) 10/65 kA, CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)	10/100 kA, Fuse, SCCR (UL/CSA) 125/100 A, Class J, max. Fuse, SCCR (UL/CSA) 10/22 kA, CB, SCCR (UL/CSA)

	50/32 A, max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V	100 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V	50 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V	35 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V	35 A gG/gL
SPECIAL PURPOSE RATING OF BALLAST ELECTRICAL DISCHARGE LAMPS	40 A (480V 60Hz 3phase, 277V 60Hz 1phase) 40 A (600V 60Hz 3phase, 347V 60Hz 1phase)
SPECIAL PURPOSE RATING OF DEFINITE PURPOSE RATING	25 A, FLA 480 V 60 Hz 3- ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 150 A, LRA 480 V 60 Hz 3- ph, 100,000 cycles acc. to UL 1995, (UL/CSA)
SPECIAL PURPOSE RATING OF ELEVATOR CONTROL	15 HP, 600 V 60 Hz 3-ph, (UL/CSA) 3 HP, 200 V 60 Hz 3-ph, (UL/CSA) 17 A, 600 V 60 Hz 3-ph, (UL/CSA) 5 HP, 240 V 60 Hz 3-ph, (UL/CSA) 10 HP, 480 V 60 Hz 3-ph, (UL/CSA) 11 A, 200 V 60 Hz 3-ph, (UL/CSA) 15.2 A, 240 V 60 Hz 3-ph, (UL/CSA) 14 A, 480 V 60 Hz 3-ph, (UL/CSA)
SPECIAL PURPOSE RATING OF REFRIGERATION CONTROL (CSA ONLY)	240 A, LRA 480 V 60 Hz 3phase; (CSA) 30 A, FLA 600 V 60 Hz 3phase; (CSA) 40 A, FLA 480 V 60 Hz 3phase; (CSA) 180 A, LRA 600 V 60 Hz 3phase; (CSA)
SPECIAL PURPOSE	40 A, 480 V 60 Hz 3phase,

RATING OF RESISTANCE AIR HEATING	277 V 60 Hz 1phase, (UL/CSA) 40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)
SPECIAL PURPOSE RATING OF TUNGSTEN INCANDESCENT LAMPS	40 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) 40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)
CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN)	45 A
CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)	41 A
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	39 A
RATED OPERATIONAL POWER AT AC-3, 440 V, 50 HZ	15.5 kW
RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	17.5 kW
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	14 kW
ACTUATING VOLTAGE	24 V DC
ALTITUDE	Max. 2000 m
OPERATING VOLTAGE AT AC, 50 HZ - MIN	24 V
OPERATING VOLTAGE AT AC, 50 HZ - MAX	690 V
OPERATING VOLTAGE AT AC, 60 HZ - MIN	24 V
OPERATING VOLTAGE AT AC, 60 HZ - MAX	690 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

