



Eaton 123734

Eaton Moeller series IZMX/INX - ACB. Shunt release (for power circuit breaker);(2) 220-240VAC/DC

□□□□

PRODUCT NAME	Eaton Moeller series IZMX/INX shunt release
CATALOG NUMBER	123734
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.113 kg
COMPLIANCES	RoHS conform

□□□□

USED WITH	INX16..., INX40... IZMX16..., IZMX40...
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	240 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	208 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	240 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	208 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	250 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	220 V
ACCESSORY/SPARE PART TYPE	Remote switching
CURRENT RATING - MAX	0.034 A (maximum holding current)
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE (END VALUE) - MAX	0 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
INITIAL VALUE OF THE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
NUMBER OF ACTUATION PER MINUTE - MAX	3
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
VOLTAGE TYPE	AC/DC
CIRCUIT BREAKER TOTAL	22 ms (Us = 100%)

□□

[eaton-circuit-breaker-izmx-inx-acb-3d-drawing-010.eps](#)

SWITCHING TIME	
CONTROL VOLTAGE OPERATING RANGE	0.7 - 1.1 x Us
	208 - 240 V AC (50/60 Hz)
	208 - 250 V DC
TYPE	Accessory
SPECIAL FEATURES	• Cannot be combined with an undervoltage release.
	• Limited to 3/min due to the high pick-up current for 35 ms.
	• Please note - the circuit-breaker's switching frequency = 60/h
POWER CONSUMPTION	9 VA/W AC/DC
RATED OPERATIONAL CURRENT	0.034 A (maximum holding current)
SUITABLE FOR	Off-load switch Power circuit breaker

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

