



## Eaton 118705

Eaton ESR5 Safety relay emergency stop/protective door/light curtain, 24 V DC, 4 enabling paths(2del.)

□□□□

<b>PRODUCT NAME</b>	Eaton ESR5 Safety relay
<b>CATALOG NUMBER</b>	118705
<b>PRODUCT LENGTH/DEPTH</b>	114.5 mm
<b>PRODUCT HEIGHT</b>	99 mm
<b>PRODUCT WIDTH</b>	22.5 mm
<b>PRODUCT WEIGHT</b>	0.171 kg
<b>CERTIFICATIONS</b>	EN ISO 13849-1 CE CSA Class No.: 3211-83; 3211-03 IEC 61508, Parts 1-7 UL File No.: E29184 UL 508 UL report applies to both US and Canada IEC/EN 60204 EN 50178 Certified by UL for use in Canada IEC 62061 2014/30/EU CSA-C22.2 No. 14-95 UL Category Control No.: NKCR; NKCR7 UL Machines 2006/42/EG



Powering Business Worldwide

**TYPE**

- Emergency stop category 1; emergency switching off
- Feedback circuit
- Light curtain
- Protective door

**MOUNTING METHOD**

Top-hat rail fixing  
(according to IEC/EN 60715, 35 mm)  
Rail mounting possible

**OPERATING TEMPERATURE - MAX**

45 °C

**OPERATING TEMPERATURE - MIN**

-20 °C

**FEATURES**

Automatic start  
Manual start  
Basic insulation  
2 Non-delayed enable current paths

**10.10 TEMPERATURE RISE**

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**10.11 SHORT-CIRCUIT RATING**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.12 ELECTROMAGNETIC COMPATIBILITY**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.13 MECHANICAL FUNCTION**

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

**10.2.2 CORROSION RESISTANCE**

Meets the product standard's requirements.

**10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES**

Meets the product standard's requirements.

**10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT**

Meets the product standard's requirements.

**10.2.3.3 RESIST. OF**

Meets the product

**CHARACTERISTIC CURVE**

[eaton-safety-relays-esr5-safety-relay-characteristic-curve-005.eps](#)

**DECLARATIONS OF CONFORMITY**

[eaton-safety-relay-declaration-of-conformity-uk251140en.pdf](#)

## □□□

[eaton-safety-relays-esr5-safety-relay-wiring-diagram-013.eps](#)

[eaton-safety-relays-esr5-safety-relay-wiring-diagram-014.eps](#)

[eaton-safety-relays-esr5-safety-relay-wiring-diagram-015.eps](#)

## □□

[eaton-safety-relays-relay-esr5-safety-relay-dimensions-002.eps](#)

[eaton-general-esr5-safety-relay-symbol-002.eps](#)

[eaton-safety-relays-relay-esr5-safety-relay-3d-drawing.eps](#)

[eaton-general-esr5-safety-relay-symbol.eps](#)

<b>INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>ELECTRIC CONNECTION TYPE</b>	Screw connection
<b>FITTED WITH:</b>	Approval for TÜV Start input Selectable cross-circuit detection Detachable clamps Feedback circuit Approval according to UL
<b>POLLUTION DEGREE</b>	2
<b>CLIMATIC PROOFING</b>	Dry heat to IEC 60068-2-2 Damp heat, constant, to IEC 60068-2-3 Cold to EN 60068-2-1

<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4000 V AC
<b>AIR PRESSURE</b>	795 - 1080 hPa (operation)
<b>ALTITUDE</b>	Max. 2000 m
<b>CATEGORY (EN 954-1)</b>	4
<b>DEGREE OF PROTECTION</b>	Terminals: IP20 IP20 Installation location: ≥ IP54  Enclosure: IP20
<b>ENVIRONMENTAL CONDITIONS</b>	Clearance in air and creepage distances according to EN 60947-1, UL 508, CSA C22.2, No. 14- 95 Condensation: Non- condensing
<b>NUMBER OF INPUTS</b>	One- and two-channel
<b>FUNCTIONS</b>	1-channel 2-channel Time function
<b>SAFETY PERFORMANCE LEVEL (EN ISO 13849-1)</b>	Level e
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	45 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-20 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID</b>	0 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID</b>	0 W
<b>LIFETIME</b>	240 month
<b>NOMINAL CURRENT</b>	3.5 A
<b>NUMBER OF OUTPUTS (SAFETY RELATED, DELAYED) WITH CONTACT</b>	2
<b>NUMBER OF OUTPUTS (SAFETY RELATED, DELAYED, SEMICONDUCTORS)</b>	0
<b>NUMBER OF OUTPUTS</b>	2

<b>(SAFETY RELATED, UNDELAYED) WITH CONTACT</b>	
<b>NUMBER OF OUTPUTS (SAFETY RELATED, UNDELAYED, SEMICONDUCTORS)</b>	0
<b>NUMBER OF OUTPUTS (SIGNALING FUNCTION, DELAYED) WITH CONTACT</b>	0
<b>NUMBER OF OUTPUTS (SIGNALING FUNCTION, DELAYED, SEMICONDUCTORS)</b>	0
<b>NUMBER OF OUTPUTS (SIGNALING FUNCTION, UNDELAYED) WITH CONTACT</b>	0
<b>NUMBER OF OUTPUTS (SIGNALING FUNCTION, UNDELAYED, SEMICONDUCTORS)</b>	0
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX</b>	26.4 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX</b>	26.4 V
<b>SCREWDRIVER SIZE</b>	0.6 x 3.5 mm, Terminal screws 2, Terminal screw, Pozidriv screwdriver
<b>VOLTAGE TYPE</b>	DC
<b>CONNECTION TYPE</b>	M3 screw terminals
<b>MOUNTING POSITION</b>	As required
<b>BREAKING POWER</b>	144 W max., resistive load ( $\tau = 0$ ms), at 24 V DC 42 W max., inductive load ( $\tau = 40$ ms), at 24 V DC 88 W max., resistive load ( $\tau = 0$ ms), at 220 V DC 1500 VA, max., resistive load ( $\tau = 0$ ms), at 250 V AC  23 W max., inductive load ( $\tau = 40$ ms), at 220 V DC 288 W max., resistive load ( $\tau = 0$ ms), at 48 V DC 33 W max., inductive load ( $\tau = 40$ ms), at 48 V DC

	25 W max., inductive load ( $\tau = 40$ ms), at 110 V DC 90 W max., resistive load ( $\tau = 0$ ms), at 110 V DC
<b>OVERVOLTAGE CATEGORY</b>	III
<b>SHORT-CIRCUIT PROTECTION RATING</b>	10A gL/gG, NEOZED (N/O), Output fuse, External, Output data 6A gL/gG, NEOZED (N/C), Output fuse, External, Output data
<b>DUTY FACTOR</b>	100 %
<b>OFF-DELAY</b>	0.1 - 30 s ( $\pm 40$ %, K3, K4 adjustable)
<b>EMITTED INTERFERENCE</b>	According to EN 61000-6-4
<b>CURRENT CONSUMPTION</b>	75 mA, DC
<b>MATERIAL</b>	Contacts: silver tin oxide, gold plated (AgSnO <sub>2</sub> , 0.2 $\mu$ m Au) Enclosure: Polyamide (PA), not reinforced
<b>INTERFERENCE IMMUNITY</b>	According to EN-61000-6-2 According to EN 662061_x
<b>TIGHTENING TORQUE</b>	0.6 Nm, Screw terminals
<b>MOUNTING WIDTH</b>	22.5 mm
<b>SUITABLE FOR</b>	Monitoring of position switches Module used to safely interrupt electrical circuits Safety relay for monitoring emergency stop and protective door switch Monitoring of optoelectronic protection equipment Monitoring of emergency-stop circuits Safety position switch with mechanical securing action LS-S...MT-ZBZ
<b>RELATIVE HUMIDITY</b>	< 75 %
<b>LED INDICATOR</b>	Status indication of SmartWire-DT network: Green LED
<b>PICK-UP TIME</b>	150 ms typ. (at $U_e$ in automatic mode) 150 ms typ. (controlled start, K1, K2 - for UN manual operation) 150 ms typ. (controlled start, K1, K2 - for UN

	automatic mode) 150 ms typ. (at U <sub>e</sub> in manual mode)
<b>LIFESPAN, MECHANICAL</b>	10,000,000 Operations
<b>INPUT</b>	∞ ms, Simultaneity for inputs 1/2
<b>RECOVERY TIME</b>	330 ms (restart)
<b>RESISTANCE</b>	500 Ω (impedance)
<b>INRUSH CURRENT</b>	0.025 - 6 A
<b>MODEL</b>	Basic device
<b>SAFETY TYPE (IEC 61496-1)</b>	None
<b>SHORT-CIRCUIT CURRENT</b>	0.1 A, Input data
<b>VIBRATION RESISTANCE</b>	10 - 150 Hz, Amplitude: 0.15 mm, Acceleration: 2 g, (IEC/EN 60068-2-6)
<b>SAFETY PARAMETER (EN ISO 13849-1)</b>	400,000 switching cycles, B10d Cat. 4, Category PL e, Performance level
<b>TERMINAL CAPACITY</b>	2 x (0.2 – 1) mm <sup>2</sup> , solid 24 - 12 AWG, solid or stranded 1 x (0.2 – 2.5) mm <sup>2</sup> , solid 2 x (0.25 – 1) mm <sup>2</sup> , flexible with ferrule 1 x (0.25 – 2.5) mm <sup>2</sup> , flexible with ferrule
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN</b>	20.4 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	24 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	0 V
<b>RATED INSULATION VOLTAGE (UI)</b>	250 V
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	0 A
<b>RELEASE-DELAY - MAX</b>	30 s
<b>RELEASE-DELAY - MIN</b>	0.1 s
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	7.8 W
<b>STRIPPING LENGTH (MAIN CABLE)</b>	7 mm
<b>SWITCHING VOLTAGE</b>	250 V

<b>PRODUCT CATEGORY</b>	Electronic safety relays
<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
<b>SIL (IEC 61508)</b>	3
<b>PERMISSIBLE TOTAL CABLE RESISTANCE</b>	500 $\Omega$ (input and starting circuits for UN)
<b>POWER LOSS</b>	Normally 7.8 W
<b>POWER SUPPLY CIRCUIT</b>	1.8 W (DC operated)
<b>PROOFTEST</b>	240 Months (High Demand)
<b>QUADRATIC SUMMATION CURRENT</b>	55 A <sup>2</sup> ( $I_{TH}^2 = I_1^2 + I_2^2 + I_3^2 + I_4^2 + I_5^2$ )
<b>RATED OPERATIONAL VOLTAGE</b>	24 V DC (power supply) Approx. 24 V DC at input, starting and feedback circuit 230 V AC
<b>RESET TIME</b>	Normally 100 ms (delayed contacts) 20 ms (non-delayed contacts)
<b>SAFETY PARAMETER (IEC 62061)</b>	SIL 3 only for high demand requirements, Safety integrity level Cat. 4, Category 18 x 10 <sup>-10</sup> , PFHd, Probability of failure per hour SIL 3, Safety integrity level SILCL 3, Safety integrity level claim limit SIL 3, Safety integrity level, In accordance with IEC 61508
<b>UNINTERRUPTED CURRENT</b>	6 A N/O, Limiting continuous current 6 A N/C, Limiting continuous current
<b>SHORT-CIRCUIT PROTECTION</b>	Fuse 10 A gL/gG NEOZED, For output circuits, External
<b>STOP CATEGORY (IEC 60204)</b>	0 1
<b>SWITCHING CAPACITY</b>	3 A at 3600 O/h, DC-13 at 24 V, Outputs 5 A at 3600 O/h, AC-15 at 230 V, Outputs 0.4 W In accordance with IEC 60947-5-1, Outputs
<b>SWITCHING FREQUENCY</b>	Max. 0.5 Hz, Input data



<b>POWER CONSUMPTION</b>	7.8 W
<b>CONTROL VOLTAGE 1 - MIN</b>	24 V
<b>CONTROL VOLTAGE 1 - MAX</b>	24 V
<b>CONTROL VOLTAGE 2 - MIN</b>	24 V
<b>CONTROL VOLTAGE 2 - MAX</b>	24 V
<b>CONTROL VOLTAGE 1 TYPE</b>	DC
<b>CONTROL VOLTAGE 2 TYPE</b>	DC
<b>VOLTAGE TYPE OF SUPPLY VOLTAGE</b>	AC
<b>VOLTAGE TYPE OF OPERATING VOLTAGE</b>	DC
<b>RATED SWITCH CURRENT</b>	5 A
<b>SUPPLY VOLTAGE AT AC, 50 HZ - MIN</b>	0 V
<b>SUPPLY VOLTAGE AT AC, 50 HZ - MAX</b>	0 V
<b>SUPPLY VOLTAGE AT AC, 60 HZ - MIN</b>	0 V
<b>SUPPLY VOLTAGE AT AC, 60 HZ - MAX</b>	0 V
<b>SUPPLY VOLTAGE AT DC - MIN</b>	24 V
<b>SUPPLY VOLTAGE AT DC - MAX</b>	24 V
<b>OPERATING VOLTAGE AT AC, 50 HZ - MIN</b>	0 V
<b>OPERATING VOLTAGE AT AC, 50 HZ - MAX</b>	0 V
<b>OPERATING VOLTAGE AT AC, 60 HZ - MIN</b>	0 V
<b>OPERATING VOLTAGE AT AC, 60 HZ - MAX</b>	0 V
<b>OPERATING VOLTAGE AT DC - MIN</b>	24 V
<b>OPERATING VOLTAGE AT DC - MAX</b>	24 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

