

Eaton 125NHG01BI-400

Eaton Bussmann series low voltage NH Fuse,
125 A, 400 V, 120 kAIC, 8.8 Watt, Blade end

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	125NHG01BI-400
UPC	051712233477
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	58 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	308 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	125 A
FITTED WITH:	Insulated metal gripping lugs
FUSE SIZE	NH01
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	400 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
WATT LOSSES	8.8 W
CONNECTION	Blade end
CONSTRUCTION	NH01
CONSTRUCTION SIZE	NH01
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	Microswitch 170H0235
MATERIAL	Ceramic body
PACKAGING TYPE	Standard
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	Fuse
APPLICATION	• industrial • Utilities, Solar, Wind
RATED SWITCHING CAPACITY AC	120 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

