



Eaton 119189

Eaton xEnergy Basic LV systems Low voltage switchgear. Floor standing distribution board with three-point turn-lock, W = 800 mm, H = 2060 mm, D = 250 mm

□□□□

PRODUCT NAME	Eaton xEnergy Basic empty enclosure
CATALOG NUMBER	119189
PRODUCT LENGTH/DEPTH	250 mm
PRODUCT HEIGHT	2060 mm
PRODUCT WIDTH	800 mm
PRODUCT WEIGHT	36 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

TYPE	Basic device
FEATURES	Mounting plate depth-adjustable EMC-version
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility.
10.13 MECHANICAL FUNCTION	Meets the product standard's requirements.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Not relevant to indoor installations.
10.2.5 LIFTING	Met; assembled and secured as per the latest applicable instruction leaflet.
10.2.6 MECHANICAL IMPACT	IK08
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	IP30
10.4 CLEARANCES AND CREEPAGE DISTANCES	Is the panel builder's responsibility.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	< 0.1 Ω; meets the product standard's requirements.
10.6 INCORPORATION OF SWITCHING DEVICES AND	Is the panel builder's responsibility.

	bp f 800 20 2 5.stp
MCAD MODEL	bp f 800 20 2 5.dwg

COMPONENTS	
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Ui = 440 V AC
10.9.3 IMPULSE WITHSTAND VOLTAGE	4 kV
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Does not apply to metal enclosures.
FITTED WITH:	Door
SURFACE FINISHING	With powder coating Powder coating
DEGREE OF PROTECTION	IK08 (impact resistance) IP30 Other IK08
GRADE MATERIAL	Sheet steel
HEAT DISS. AMBIENT 35°C DELTA T:20°C FREE STAND INDIVID. ENCL. TOP (IEC 60890)	193 W
HEAT DISS. AMBIENT 35°C DELTA T: 20°C FREE STAND MIDDLE ENCL. TOP (IEC 60890)	184 W
HEAT DISS. AMBIENT 35°C DELTA T:20°C FREE STAND STARTING ENCL. TOP (IEC 60890)	188 W
HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)	177 W
HEAT DISS. AMBIENT 35°C DELTA T: 20°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)	157 W
HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)	170 W
HEAT DISS. AMBIENT 35°C DELTA T:35°C FREE STAND INDIVID. ENCL. TOP (IEC 60890)	387 W
HEAT DISS. AMBIENT 35°C DELTA T: 35°C FREE STAND MIDDLE ENCL.	370 W

TOP (IEC 60890)	
HEAT DISS. AMBIENT 35°C DELTA T:35°C FREE STAND STARTING ENCL. TOP (IEC 60890)	378 W
HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)	355 W
HEAT DISS. AMBIENT 35°C DELTA T: 35°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)	315 W
HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)	341 W
MATERIAL QUALITY	Other
COLOR	Gray Light gray (RAL 7035)
COVER/DOOR TYPE	Three-point turn-lock
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	0 N
NUMBER OF LOCKS	1
RAL-NUMBER	7035
APPLICATION	Indoor (installation site)
MATERIAL	Sheet steel Steel
MOUNTING METHOD	Floor standing distribution board Detached
FUNCTIONS	Basic device
INSTALLATION TYPE	Floor installation possible
NUMBER OF COVERS/DOORS	1
SUITABLE FOR	Metrical mounting
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	0 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	0 N
THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890	0 W
NUMBER OF CONNECTOR HOLES	0

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

