



□□□□

## Eaton 121500

Eaton C22 Pushbutton, flat, momentary, 2 N/C, black, Screw connection, Bezel: black

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series C22 Pushbutton
<b>CATALOG NUMBER</b>	121500
<b>PRODUCT LENGTH/DEPTH</b>	55 mm
<b>PRODUCT HEIGHT</b>	30 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	0.021 kg
<b>CERTIFICATIONS</b>	UL 508 IEC/EN 60947-5-1 UL Category Control No.: NKCR CSA certified UL Listed CSA-C22.2 No. 14-05 and 94-M91 UL File No.: E29184 CSA File No.: 165628 CE marking CSA Class No.: 321103 VDE 0660
<b>CATALOG NOTES</b>	Contacts with safety function, by positive opening to IEC/EN 60947-5-1



Powering Business Worldwide

□□□□

<b>TYPE</b>	Pushbutton actuator
<b>ACTUATOR COLOR</b>	Black
<b>FEATURES</b>	Positive opening
<b>ACTUATOR FUNCTION</b>	Spring-return Momentary
<b>ELECTRIC CONNECTION TYPE</b>	Screw connection
<b>FITTED WITH:</b>	Front ring
<b>OPERATING FREQUENCY</b>	3600 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4000 V AC
<b>BEZEL COLOR</b>	Black
<b>ACTUATING FORCE</b>	5 N
<b>ACTUATOR DIAMETER</b>	29.7 mm
<b>ACTUATOR TRAVEL AND ACTUATION FORCE (DIN EN 60947-5-1)</b>	4.65 mm
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>FORCE FOR POSITIVE OPENING - MIN</b>	30 N
<b>KNOB TRAVEL</b>	5.7 mm
<b>NUMBER OF COMMAND POSITIONS</b>	1
<b>NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)</b>	2
<b>NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>BEZEL MATERIAL</b>	Plastic
<b>DESIGN</b>	Flat
<b>MOUNTING POSITION</b>	As required
<b>RATED CONDITIONAL</b>	1 kA

□□

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-pushbutton-declaration-of-conformity-uk250928en.pdf</a>
<b>ECAD MODEL</b>	<a href="#">DA-CE-ETN.C22S-D-S-K02</a>
<b>MCAD MODEL</b>	<a href="#">eaton-c22-d-compact-3d-model.stp</a> <a href="#">eaton-pushbuttons-mcad-drawings-c22-d-compact.dwg</a>
□□□□□	<a href="#">eaton-rmq-titan-c22-pv-compact-program-emergency-buttons-instruction-leaflet-il04716025z.pdf</a>
□□□	<a href="#">eaton-operating-pushbutton-wiring-diagram-005.eps</a>
□□□□□	<a href="#">eaton-operating-adapter-key-operated-actuator-contact-travel-diagram.eps</a>
	<a href="#">eaton-operating-actuation-pushbutton-dimensions-002.eps</a>
□□	<a href="#">eaton-operating-button-symbol-005.eps</a> <a href="#">eaton-operating-pushbutton-3d-drawing.eps</a>

