



Eaton 135190

Eaton CR Installation contactor, 25A, 230V
AC, 2NO+2NC

□□□□

PRODUCT NAME	Eaton CR contactor
CATALOG NUMBER	135190
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.241 kg
COMPLIANCES	RoHS conform

□□□□

AMPERAGE RATING	25 A
FEATURES	Additional equipment possible
DEGREE OF PROTECTION	IP20
INCANDESCENT LAMP LOAD - MAX	2200 W
LOAD FLUORESCENT LAMP - MAX	1200 VA
LOAD FLUORESCENT LAMP (DUO CIRCUIT) - MAX	1440 VA
LOAD FLUORESCENT LAMP (PARALLEL COMPENSATED) - MAX	400 VA
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF MODULAR SPACINGS	2
RATED OPERATING VOLTAGE (UE) - MAX	400 V
RATED OPERATING VOLTAGE (UE) - MIN	400 V
UTILITY CATEGORY	1
VOLTAGE RATING (EXCITATION) - MAX	253 V
VOLTAGE RATING (EXCITATION) - MIN	195.5 V
BUILT-IN DEPTH	60 mm
VOLTAGE TYPE	AC
UTILIZATION CATEGORY (ACCORDING TO EN IEC 60947-4-1)	AC-1

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

