

Eaton 124265

Eaton Moeller series IZMX/INX - ACB. Eaton Moeller series IZMX/INX - ACB. Motor operator, 110-125 VAC/DC, Acc

PRODUCT NAME	Eaton Moeller series IZMX/INX motor operator
CATALOG NUMBER	124265
PRODUCT LENGTH/DEPTH	200 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	150 mm
PRODUCT WEIGHT	0.905 kg
COMPLIANCES	RoHS conform

USED WITH	INX16... IZMX16...
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	127 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	125 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	110 V
ACCESSORY/SPARE PART TYPE	Remote switching
CURRENT RATING - MAX	2 V AC / 1 V DC (maximum holding current)
PICK-UP POWER CONSUMPTION AT 35 MS - MAX	3 VA/W
STARTING CURRENT RATING	6 A AC 50/60 Hz, 5 A DC
SWITCH DRIVE TYPE	Motor drive
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF ACTUATION PER MINUTE - MAX	3
VOLTAGE TYPE	AC/DC
CONTROL VOLTAGE OPERATING RANGE	110 - 127 V AC (50/60 Hz) 0.85 - 1.1 x Us 110 - 125 V DC
TYPE	Accessory
SPECIAL FEATURES	• Signalling switch for "Spring-operated stored energy mechanism tensioned"

[eaton-circuit-breaker-izmx-inx-motor-operator-3d-drawing-002.eps](#)

message is included as standard.

- Switching frequency = 60/h
- The motor automatically tensions the spring force storage mechanism for remote or local actuation.
- A signaling switch for the „Spring force storage charged” message is included as standard.

POWER CONSUMPTION

280 AC / 150 DC
280 VA AC 50/60 Hz
150 W DC

**NECESSARY TIME FOR
CHARGING SPRING-
OPERATED STORED
ENERGY MECHANISM AT
1 X US**

3 s DC
3 s AC 50/60 Hz

**RATED OPERATIONAL
CURRENT**

1 A DC
2 A AC 50/60 Hz
2 V AC / 1 V DC (maximum
holding current)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

