



## Eaton 135196

Eaton CR Installation contactor, 25A, 12V AC, 4NO

### □□□□

|                             |                    |
|-----------------------------|--------------------|
| <b>PRODUCT NAME</b>         | Eaton CR contactor |
| <b>CATALOG NUMBER</b>       | 135196             |
| <b>PRODUCT LENGTH/DEPTH</b> | 75 mm              |
| <b>PRODUCT HEIGHT</b>       | 80 mm              |
| <b>PRODUCT WIDTH</b>        | 36 mm              |
| <b>PRODUCT WEIGHT</b>       | 0.224 kg           |
| <b>COMPLIANCES</b>          | RoHS conform       |

□□□□

|                                                      |                               |
|------------------------------------------------------|-------------------------------|
| AMPERAGE RATING                                      | 25 A                          |
| FEATURES                                             | Additional equipment possible |
| DEGREE OF PROTECTION                                 | IP20                          |
| INCANDESCENT LAMP LOAD - MAX                         | 2200 W                        |
| LOAD FLUORESCENT LAMP - MAX                          | 1200 VA                       |
| LOAD FLUORESCENT LAMP (DUO CIRCUIT) - MAX            | 1440 VA                       |
| LOAD FLUORESCENT LAMP (PARALLEL COMPENSATED) - MAX   | 400 VA                        |
| NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)        | 0                             |
| NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)          | 4                             |
| NUMBER OF MODULAR SPACINGS                           | 2                             |
| RATED OPERATING VOLTAGE (UE) - MAX                   | 400 V                         |
| RATED OPERATING VOLTAGE (UE) - MIN                   | 400 V                         |
| UTILITY CATEGORY                                     | 1                             |
| VOLTAGE RATING (EXCITATION) - MAX                    | 13.2 V                        |
| VOLTAGE RATING (EXCITATION) - MIN                    | 10.2 V                        |
| BUILT-IN DEPTH                                       | 60 mm                         |
| VOLTAGE TYPE                                         | AC                            |
| UTILIZATION CATEGORY (ACCORDING TO EN IEC 60947-4-1) | AC-1                          |

□□

