

Eaton 124292

Eaton Moeller series IZMX/INX - ACB. Motor operator 48 VDC, 40, +

PRODUCT NAME	Eaton Moeller series IZMX/INX motor operator
CATALOG NUMBER	124292
PRODUCT LENGTH/DEPTH	200 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	150 mm
PRODUCT WEIGHT	1.425 kg
COMPLIANCES	RoHS conform

USED WITH	IZMX40... INX40...
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	48 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	48 V
ACCESSORY/SPARE PART TYPE	Remote switching
CURRENT RATING - MAX	3 A (maximum holding current)
PICK-UP POWER CONSUMPTION AT 35 MS - MAX	3 VA/W
STARTING CURRENT RATING	12 A DC
SWITCH DRIVE TYPE	Motor drive
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF ACTUATION PER MINUTE - MAX	3
VOLTAGE TYPE	DC
CONTROL VOLTAGE OPERATING RANGE	48 V DC 0.85 - 1.1 x Us
TYPE	Accessory
SPECIAL FEATURES	<ul style="list-style-type: none"> • DC • Signalling contact and an indicator at the front of the circuit breaker for "Spring-operated

-
- stored energy mechanism armed" message are included as standard.
 - Switching frequency = 60/h

POWER CONSUMPTION	175 VA/W AC/DC 175 W DC
--------------------------	----------------------------

NECESSARY TIME FOR CHARGING SPRING-OPERATED STORED ENERGY MECHANISM AT 1 X US	3 s DC
--	--------

RATED OPERATIONAL CURRENT	3 A (maximum holding current) 3 A DC
----------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

