



Eaton 125315

Eaton SPX Variable frequency drive, 600 V AC, 3-phase, 30 kW, IP54, Radio interference suppression filter, OLED display, FR7

□□□□

PRODUCT NAME	Eaton SPX variable frequency drive
CATALOG NUMBER	125315
PRODUCT LENGTH/DEPTH	640 mm
PRODUCT HEIGHT	257 mm
PRODUCT WIDTH	237 mm
PRODUCT WEIGHT	35 kg

CERTIFICATIONS	DNV RCM UL report applies to both US and Canada IEC/EN 61800-3 UL UL Category Control No.: NMMS, NMMS2, NMMS7, NMMS8 CE CSA Class No.: 3211-06 UL File No.: E134360 Certified by UL for use in Canada IEC/EN61800-5 CUL RoHS, ISO 9001 IEC/EN61800-3 Specification for general requirements: IEC/EN 61800-2 CSA-C22.2 No. 14 Safety: EN 61800-5-1: 2003 UL 508C
-----------------------	--



Powering Business Worldwide

PRODUCT CATEGORY	Variable frequency drives
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.

□□□□□	IL04020008Z
□□	eaton-frequency-inverter-dimensions-006.eps

10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	OLED display Internal DC link Radio interference suppression filter DC link choke IGBT inverter
CLIMATIC PROOFING	< 95 % relative humidity, no condensation, no corrosion, no dripping water
CONNECTION TO SMARTWIRE-DT	No
OPERATING MODE	Optional: Vector control with feedback (CLV) U/f control Sensorless vector control (SLV)
FRAME SIZE	FR7
ALTITUDE	Max. 1000 m Above 1000 m with 1 % performance reduction per 100 m Max. 3000 m
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	No
APPLICATION IN INDUSTRIAL AREA PERMITTED	No
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C

AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	50 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
MOUNTING POSITION	Vertical
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
HEAT DISSIPATION DETAILS	Operation (with 150 % overload)
RATED OPERATIONAL POWER AT 690 V, 50 HZ	30 kW
RATED OPERATIONAL POWER AT 690 V, 50 HZ, 110% OVERLOAD	37 kW
RESOLUTION	0.01 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
VOLTAGE RATING - MAX	690 VAC
COMMUNICATION INTERFACE	CANopen®, optional LonWorks, optional PROFIBUS-DP DeviceNet, optional Modbus-TCP, optional BACnet/IP, optional BACnet MS/TP, optional EtherCAT, optional Ethernet IP, optional Modbus-RTU, optional PROFINET, optional
CONVERTER TYPE	Other
DEGREE OF PROTECTION	IP54 NEMA Other
ASSIGNED MOTOR CURRENT IM AT 690 V, 50 HZ, 110% OVERLOAD	39 A
ASSIGNED MOTOR CURRENT IM AT 690 V, 50 HZ, 150% OVERLOAD	32 A
ASSIGNED MOTOR CURRENT IM AT 690 V, 60 HZ, 110% OVERLOAD	36 A

ASSIGNED MOTOR CURRENT IM AT 690 V, 60 HZ, 150% OVERLOAD	28 A
SYSTEM CONFIGURATION TYPE	AC supply systems with earthed center point
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ASSIGNED MOTOR POWER AT 690 V, 60 HZ	30 HP
ASSIGNED MOTOR POWER AT 690 V, 60 HZ, 110% OVERLOAD	40 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	750 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OUTPUT VOLTAGE (U2)	600 V AC, 3-phase 690 V AC, 3-phase
NUMBER OF INPUTS (ANALOG)	2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)
NUMBER OF INPUTS (DIGITAL)	6 (parameterizable, max. 30 V DC)
RADIO INTERFERENCE CLASS	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.
NUMBER OF OUTPUTS (DIGITAL)	1 (parameterizable, 48 V DC/50 mA)
NUMBER OF RELAY OUTPUTS	2 (parameterizable, N/O, 8 A (24 V DC) / 8 A (250 V AC) / 0,4 A (125 V DC))
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 10 mA)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 250 mA)
SUPPLY FREQUENCY	50/60 Hz
MAINS VOLTAGE - MAX	690 V
MAINS VOLTAGE - MIN	525 V
NUMBER OF OUTPUTS (ANALOG)	1
OUTPUT FREQUENCY - MAX	320 Hz
OUTPUT FREQUENCY -	0 Hz

MIN	
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	1.5 kHz, 1 - 6 kHz adjustable, fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	690 V AC, 3-phase 600 V AC, 3-phase
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD	41 A
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	34 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	34 A

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

