

Eaton 139551

Eaton Moeller® series DILM Contactor, 380 V 400 V 110 kW, 2 N/O, 2 NC, RDC 60: 48 - 60 V DC, DC operation, Screw connection

PRODUCT NAME	Eaton Moeller® series DILM Contactor
CATALOG NUMBER	139551
PRODUCT LENGTH/DEPTH	158 mm
PRODUCT HEIGHT	190 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	3.54 kg
CERTIFICATIONS	UL 60947-4-1 CSA File No.: 2389068 VDE 0660 CSA Class No.: 3211-04 UL Category Control No.: NLDX CE UL File No.: E29096 CSA-C22.2 No. 60947-4-1- 14 UL IEC/EN 60947 IEC/EN 60947-4-1 CSA
CATALOG NOTES	<ul style="list-style-type: none">• Contacts according to EN 50012• Also tested according to AC-3e up to 500 V.• Also suitable for motors with efficiency class IE3.• Conventional thermal current I_{th} of main contacts (1-pole, open) at 60°

ACCESSORIES	Fitting options auxiliary contacts: on the side: 2 x DILM1000-XHI(V)11-SI; 2 x DILM1000-XHI11-SA
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

CHARACTERISTIC CURVE	eaton-contactors-component-dilm-characteristic-curve.eps
	eaton-contactors-component-dilm-characteristic-curve-002.eps
	IL03406001Z
	eaton-contactors-contact-dilm-wiring-diagram-004.eps
	eaton-contactors-dilm-dimensions-006.eps
	eaton-contactors-dilm-3d-drawing.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Suppressor circuit in actuating electronics
OPERATING FREQUENCY	200 Operations/h 3000 mechanical Operations/h (DC operated)
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	8000 V AC
UTILIZATION CATEGORY	AC-4: Normal AC induction motors: starting, plugging, reversing, inching AC-1: Non-inductive or slightly inductive loads, resistance furnaces AC-3: Normal AC induction motors: starting, switch off during running
CONNECTION	Screw terminals
AMBIENT OPERATING TEMPERATURE - MAX	60 °C

AMBIENT OPERATING TEMPERATURE - MIN	-40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-40 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	60 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	75 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	150 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	200 HP
CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)	688 A
CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)	275 A
CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)	329 A
CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1-POLE, OPEN)	788 A
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	7.67 W
APPLICATION	Contactors for Motors
PRODUCT CATEGORY	Contactors
PROTECTION	Finger and back-of-hand proof with terminal

	shroud or terminal block, Protection against direct contact when actuated from front (EN 50274)
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Rail connection
SCREWDRIVER SIZE	2, Terminal screw, Control circuit cables, Pozidriv screwdriver
VOLTAGE TYPE	DC
DEGREE OF PROTECTION	IP00
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)	3
RATED BREAKING CAPACITY AT 1000 V	760 A
RATED BREAKING CAPACITY AT 220/230 V	2250 A
RATED BREAKING CAPACITY AT 380/400 V	2250 A
RATED BREAKING CAPACITY AT 500 V	2250 A
RATED BREAKING CAPACITY AT 660/690 V	2250 A
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V

RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
DROP-OUT VOLTAGE	<p>AC operated: 0.25 x US max - 0.6 x US min, AC operated</p> <p>AC operated: 0.2 x US max - 0.4 x US min, AC operated</p> <p>DC operated: 0.2 x US max - 0.6 US min, DC operated</p> <p>DC operated: 0.15 x US min - 0.6 US max, DC operated</p>
OVERVOLTAGE CATEGORY	III
DUTY FACTOR	100 %
ELECTROMAGNETIC COMPATIBILITY	Designed for operation in industrial environments. Its use in residential environments may cause radio-frequency interference, requiring additional noise suppression.
LIFESPAN, MECHANICAL	10,000,000 Operations (DC operated)
PICK-UP VOLTAGE	0.7 - 1.2 V DC x Us
POWER CONSUMPTION, PICK-UP, 50 HZ	<p>210 VA, Pull-in power, Coil in a cold state and 1.0 x Us</p> <p>180 W, Pull-in power, Coil in a cold state and 1.0 x Us</p>
SAFE ISOLATION	1000 V AC, Between coil and contacts, According to EN 61140
POWER CONSUMPTION, PICK-UP, 60 HZ	<p>210 VA, Pull-in power, Coil in a cold state and 1.0 x Us</p> <p>180 W, Pull-in power, Coil in a cold state and 1.0 x Us</p>
SCREW SIZE	<p>M10, Terminal screw, Main connections</p> <p>M3.5, Terminal screw, Control circuit cables</p>
POWER CONSUMPTION, SEALING, 50 HZ	2.1 W, Coil in a cold state and 1.0 x Us
POWER CONSUMPTION, SEALING, 60 HZ	2.1 W, Coil in a cold state and 1.0 x Us
RATED OPERATIONAL CURRENT (IE)	220 A at up to 525 V (Individual compensation,

	three-phase capacitors, open) 133 A at 690 V (Individual compensation, three-phase capacitors, open)
INRUSH CURRENT	Max. 30 x I _e (peak)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	1 A, 250 V DC, (UL/CSA) 15 A, 600 V AC, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A600, AC operated (UL/CSA) P300, DC operated (UL/CSA)
LIFESPAN, ELECTRICAL	100,000 Operations (at Condensor operation)
TERMINAL CAPACITY (COPPER BAND)	Fixing with flat cable terminal or cable terminal blocks; See terminal capacity for cable terminal blocks
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables
SHOCK RESISTANCE	8 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 10 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 2.5) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 14, Control circuit cables 2/0 - 250 MCM, Main cables
TERMINAL CAPACITY (BUSBAR)	32 mm width, Main connection
TERMINAL CAPACITY (FLEXIBLE WITH CABLE LUG)	50 - 185 mm ²
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	250 A, Maximum motor rating (UL/CSA)

TERMINAL CAPACITY (STRANDED WITH CABLE LUG)	70 - 185 mm ²
TIGHTENING TORQUE	1.2 Nm, Screw terminals, Control circuit cables 24 Nm, Main cable connection screw/bolt
WIDTH ACROSS FLATS	16 mm
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	60 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	48 V
RATED INSULATION VOLTAGE (UI)	1000 V
RATED MAKING CAPACITY (COS PHI TO IEC/EN 60947)	2700 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 1000 V	76 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	225 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	225 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V	225 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	225 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	160 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 1000 V	55 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V	164 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V	164 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 440 V	164 A
RATED OPERATIONAL	164 A

CURRENT (IE) AT AC-4, 500 V	
RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V	120 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	225 A
RATED OPERATIONAL POWER AT AC-3, 1000 V, 50 HZ	108 kW
RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ	75 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	110 kW
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	132 kW
RATED OPERATIONAL POWER AT AC-4, 1000 V, 50 HZ	77 kW
RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ	51 kW
RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ	54 kW
RATED OPERATIONAL POWER AT AC-4, 380/400 V, 50 HZ	90 kW
RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ	96 kW
RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ	102 kW
RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ	116 kW
RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ	110 kW
RATED OPERATIONAL POWER (NEMA)	111 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	1000 V
RESISTANCE PER POLE	0.15 mΩ

STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	2.1 W
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX	60 ms
SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX	40 ms
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	700 A, max. Fuse, SCCR (UL/CSA) 10 kA, SCCR (UL/CSA) 600 A, max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)	100 kA, Fuse, SCCR (UL/CSA) 600 A, Class J, max. Fuse, SCCR (UL/CSA) 65 kA, CB, SCCR (UL/CSA) 350 A, max. CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)	350 A, max. CB, SCCR (UL/CSA) 100 kA, Fuse, SCCR (UL/CSA) 600 A, Class J, max. Fuse, SCCR (UL/CSA) 50 kA, CB, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 1000 V	200 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V	400 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V	315 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 1000 V	160 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V	315 A gG/gL
SHORT-CIRCUIT	250 A gG/gL

PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V	
SPECIAL PURPOSE RATING OF DEFINITE PURPOSE RATING	336 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 280 A, FLA 600 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 2016 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 1680 A, LRA 600 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)
CONVENTIONAL THERMAL CURRENT ITH AT 40°C (3-POLE, OPEN)	386 A
CONVENTIONAL THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)	345 A
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	315 A
RATED OPERATIONAL POWER AT AC-3, 440 V, 50 HZ	138 kW
RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	160 kW
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	150 kW
ACTUATING VOLTAGE	RDC 60: 48 - 60 V DC
ALTITUDE	Max. 2000 m

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: