



## Eaton 142786

Eaton Moeller series xPole - mRCM RCCB.  
Residual current circuit breaker (RCCB), 25A,  
4 p, 300mA, type A

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xPole - mRCM RCCB
<b>CATALOG NUMBER</b>	142786
<b>PRODUCT LENGTH/DEPTH</b>	76 mm
<b>PRODUCT HEIGHT</b>	80 mm
<b>PRODUCT WIDTH</b>	70 mm
<b>PRODUCT WEIGHT</b>	0.32 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 61008



Powering Business Worldwide

□□□□

<b>USED WITH</b>	mRCM Residual current circuit breaker, only for export Type A
<b>AMPERAGE RATING</b>	25 A
<b>FEATURES</b>	Residual current circuit-breakers only for export Additional equipment possible
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to

□□

□□□□□	<a href="#">IL019071ZU</a>
□□□□	<a href="#">eaton-protective-devices-catalog-ca20190603-en-us.pdf</a>
□□	<a href="#">eaton-circuit-breaker-xeffect-frcmm-rccb-dimensions.jpg</a>

	be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Interlocking device
<b>FREQUENCY RATING</b>	50 Hz
<b>POLLUTION DEGREE</b>	2
<b>MOUNTING METHOD</b>	DIN rail
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	2.8 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	10 kA
<b>ADMISSIBLE BACK-UP FUSE OVERLOAD - MAX</b>	25 A gG/gL
<b>SHORT-CIRCUIT RATING</b>	63 A (max. admissible back-up fuse)
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	55 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	68 mm
<b>CONNECTABLE</b>	16 mm <sup>2</sup>

<b>CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1.5 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	35 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1.5 mm <sup>2</sup>
<b>FAULT CURRENT RATING</b>	300 mA
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>	0 W
<b>DEGREE OF PROTECTION</b>	IP20
<b>IMPULSE WITHSTAND CURRENT</b>	Partly surge-proof 250 A
<b>NUMBER OF POLES</b>	Four-pole
<b>LEAKAGE CURRENT TYPE</b>	A
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• mRCM</li> <li>• Residual current circuit breaker, only for export</li> <li>• Type A</li> </ul>
<b>SPECIAL FEATURES</b>	Maximum operating temperature is 55 °C: Starting at 40 °C, the max. permissible continuous current decreases by 3% for every 1 °C
<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• Switchgear for residential and commercial applications</li> <li>• xPole - Switchgear for residential and commercial applications</li> </ul>
<b>SENSITIVITY TYPE</b>	Pulse-current sensitive
<b>RATED FAULT CURRENT - MAX</b>	0.3 A
<b>RATED FAULT CURRENT - MIN</b>	0.3 A

<b>RATED INSULATION VOLTAGE (UI)</b>	440 V
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	25 A
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	400 V
<b>RATED RESIDUAL MAKING AND BREAKING CAPACITY</b>	500 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>	0 W
<b>SURGE CURRENT CAPACITY</b>	0.25 kA
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	4
<b>VOLTAGE TYPE</b>	AC
<b>TRIPPING TIME</b>	Non-delayed
<b>RATED SHORT-CIRCUIT STRENGTH</b>	10 kA
<b>RAL-NUMBER</b>	7035
<b>COLOR</b>	Gray

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House  
 30 Pembroke Road  
 Dublin 4, □□□□  
 Eaton.com

