

Eaton 156598

Eaton Moeller series IZMX/INX - ACB. Eaton Moeller series IZMX/INX - ACB. Signalling switch ON-OFF, 2W, 16

PRODUCT NAME	Eaton Moeller series IZMX/INX auxiliary contact block
CATALOG NUMBER	156598
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.067 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC Rated EN Listed

USED WITH	IZMX16... INX16...
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	10 A
MOUNTING METHOD	Other
ACCESSORY/SPARE PART TYPE	Auxiliary contact
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF SWITCHES (FAULT SIGNAL)	0
CONNECTION	Flat plug-in
MODEL	Integrable
LAMP HOLDER	None
TYPE	Accessory
SPECIAL FEATURES	<ul style="list-style-type: none"> • 2 changeover contacts • Retrofit kit for IZMX16 circuit-breakers • For retrofitting, three additional control circuit terminal units are required. • For fixed mounting circuit-breakers #156593 and withdrawable unit circuit-breakers #156590 • Standard auxiliary switch for On-Off

- signaling.
- The basic device already contains two changeover contacts.
 - Two additional changeover contacts possible.

RATED BREAKING	0.5 A (125 V DC)
CAPACITY (INDUCTIVE	0.25 A (250 V DC)
LOAD)	10 A (250 V AC)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

