



Eaton 135681

Eaton Moeller® series E58 Diffuse reflective sensor, Sn=280mm, 4L, 10-30VDC, dark, NPN, PNP, M30, metal, M12

□□□□

PRODUCT NAME	Eaton Moeller® series E58 Diffuse reflective sensor
CATALOG NUMBER	135681
PRODUCT LENGTH/DEPTH	38.1 mm
PRODUCT HEIGHT	38.1 mm
PRODUCT WIDTH	38.1 mm
PRODUCT WEIGHT	0.23 kg
CERTIFICATIONS	CSA File No.: UL report applies to both US and Canada UL Category Control No.: NRKH, NRKH7 Certified by UL for use in Canada IEC/EN 60947-5-2 UL File No.: E166051 UL 508 CE CSA-C22.2 No. 14 UL



Powering Business Worldwide

□□□□

TYPE	Optical sensors
ELECTRIC CONNECTION TYPE	Plug-in connection
FITTED WITH:	Background suppression (Perfect Prox)
ENCLOSURE MATERIAL	Metal
ENCLOSURE TYPE	Cylinder, screw-thread
OPERATING MODE	Switching principle: Dark switching
EXPLOSION SAFETY CATEGORY FOR DUST	None
EXPLOSION SAFETY CATEGORY FOR GAS	None
FUNCTIONS	Short-circuit protection Protection against wire breakage Reflected-light beam Protection against polarity reversal
VOLTAGE TYPE	DC
WIRE SIZE	0
CONNECTION TYPE	4-wire Plug-in connection M12 x 1
CABLE SHEATH MATERIAL	Other
LIGHT TYPE	Other
DEGREE OF PROTECTION	NEMA 6 IP68
INTERFACE TYPE	Other
LED INDICATOR	Status indication of Switching state: Red LED
SWITCH FUNCTION TYPE	Other
LOAD CURRENT	Max. 100 mA (Ie)
LASER PROTECTION CLASS	None
OPERATION AGENT-SAFETY CLASS	Safety class 2
SHOCK RESISTANCE	100 g, Mechanical, Shock duration 3 ms
OPTICAL SURFACE MATERIAL	Glass
OUTPUT CURRENT (MA) - MAX	100 mA
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	30 V

□□

□□□□□	IL05305003Z
□□	eaton-proximity-switches-e58-diffuse-reflective-sensor-dimensions-002.eps
	eaton-proximity-switches-e58-diffuse-reflective-sensor-3d-drawing.eps

RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	10 V
RATED SWITCHING DISTANCE (SN)	280 mm
SENSOR LENGTH	111 mm
SWITCHING DISTANCE - MAX	318 mm
SWITCHING VOLTAGE OF OSSD AT STATE HIGH	30 V
VOLTAGE RATING - MAX	30 V
SAFETY TYPE (IEC 61496-1)	1
SWITCHING FREQUENCY	312 Hz
SENSING MODE	Dark switching
SWITCHING OUTPUT TYPE	PNP
SENSOR MATERIAL	Stainless steel
TRIANGULATION	Background fade-out
WAVELENGTH OF THE SENSOR	660 nm
PRODUCT CATEGORY	E58 Harsh Duty Series
RESPONSE TIME	1.6 ms
ADJUSTMENT RANGE - MAX	280 mm
ADJUSTMENT RANGE - MIN	0 mm
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-40 °C
DIAMETER SENSOR	30 mm
NUMBER OF CONTACT ENERGIZED OUTPUTS WITH SIGNALLING FUNCTION	0
NUMBER OF OUTPUTS (PROTECTED CONTACT ENERGIZED)	0
NUMBER OF OUTPUTS (PROTECTED SEMICONDUCTOR)	0
NUMBER OF OUTPUTS (SEMICONDUCTOR WITH SIGNALING FUNCTION)	2
ADJUSTMENT TYPE	Other

