



Eaton 135696

Eaton Moeller® series E58 Thru-beam photoelectric sensor, transmitter, Sn=250m, 4L, 10-30VDC, NPN, PNP, M30, metal, line 2m

□□□□

PRODUCT NAME	Eaton Moeller® series E58 Thru-beam photoelectric sensor
CATALOG NUMBER	135696
PRODUCT LENGTH/DEPTH	228.6 mm
PRODUCT HEIGHT	44.45 mm
PRODUCT WIDTH	165.1 mm
PRODUCT WEIGHT	0.2 kg
CERTIFICATIONS	CSA File No.: UL report applies to both US and Canada CSA-C22.2 No. 14 UL UL 508 UL Category Control No.: NRKH, NRKH7 IEC/EN 60947-5-2 CE Certified by UL for use in Canada UL File No.: E166051

□□□□	
TYPE	Optical sensors
DEVICE TYPE	Transmitter
ELECTRIC CONNECTION TYPE	Cable
FITTED WITH:	Transmitter (for combination with detector)
ENCLOSURE MATERIAL	Metal
ENCLOSURE TYPE	Cylinder, screw-thread
EXPLOSION SAFETY CATEGORY FOR DUST	None
EXPLOSION SAFETY CATEGORY FOR GAS	None
FUNCTIONS	Thru-light beam Protection against polarity reversal Short-circuit protection Protection against wire breakage
VOLTAGE TYPE	DC
WIRE SIZE	0
CONNECTION TYPE	4-wire 2 m connection cable
CABLE SHEATH MATERIAL	Polyvinyl chloride (PVC)
LIGHT TYPE	Other
DEGREE OF PROTECTION	NEMA 4 IP68
INTERFACE TYPE	Other
LED INDICATOR	Status indication of Operating voltage: Red LED
SWITCH FUNCTION TYPE	Other
LOAD CURRENT	Max. 100 mA (Ie)
LASER PROTECTION CLASS	None
OPERATION AGENT-SAFETY CLASS	Safety class 2
SHOCK RESISTANCE	100 g, Mechanical, Shock duration 3 ms
OPTICAL SURFACE MATERIAL	Glass
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	30 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	10 V

□□	
□□□□□	IL05305003Z
□□	eaton-proximity-switches-e58-diffuse-reflective-sensor-dimensions-002.eps eaton-proximity-switches-e58-3d-drawing.eps

RATED SWITCHING DISTANCE (SN)	250000 mm
SENSOR LENGTH	111 mm
SWITCHING VOLTAGE OF OSSD AT STATE HIGH	30 V
VOLTAGE RATING - MAX	30 V
SAFETY TYPE (IEC 61496-1)	1
SWITCHING FREQUENCY	312 Hz
SENSING MODE	Light-/dark switching
SWITCHING OUTPUT TYPE	NPN
SENSOR MATERIAL	Stainless steel
WAVELENGTH OF THE SENSOR	660 nm
PRODUCT CATEGORY	E58 Harsh Duty Series
RESPONSE TIME	1 ms
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-40 °C
DIAMETER SENSOR	30 mm
NUMBER OF CONTACT ENERGIZED OUTPUTS WITH SIGNALLING FUNCTION	0
NUMBER OF OUTPUTS (PROTECTED CONTACT ENERGIZED)	0
NUMBER OF OUTPUTS (PROTECTED SEMICONDUCTOR)	0
NUMBER OF OUTPUTS (SEMICONDUCTOR WITH SIGNALING FUNCTION)	0
ADJUSTMENT TYPE	Other

