



Eaton 135811

Eaton E52 Cube Series, Inductive proximity sensor, 6 - 48 V DC, 1 N/O, 1 N/C, Plug-in connection M12 x 1, 4-wire, Sn= 40 mm, Non-flush mounting, NPN, Zinc (Insulated)

□□□□

PRODUCT NAME	Eaton E52 inductive proximity sensor
CATALOG NUMBER	135811
PRODUCT LENGTH/DEPTH	41.28 mm
PRODUCT HEIGHT	79.38 mm
PRODUCT WIDTH	44.45 mm
PRODUCT WEIGHT	0.27 kg
CERTIFICATIONS	UL Category Control No.: NRKH, NRKH7 UL File No.: E166051 Certified by UL for use in Canada IEC/EN 60947-5-2 CE CSA-C22.2 No. 14 UL UL 508 CSA File No.: UL report applies to both US and Canada
CATALOG NOTES	Housing adapter



Powering Business Worldwide

□□□□

TYPE	Inductive sensor
ELECTRIC CONNECTION TYPE	Plug-in connection
ENCLOSURE MATERIAL FINISHING	Other
SURFACE FINISHING	Zinc alloy
ACTUATION TYPE	Metallic Target
ENCLOSURE MATERIAL	Plastic
ENCLOSURE TYPE	Cuboid
CATEGORY (EN 954-1)	B
EXPLOSION SAFETY CATEGORY FOR DUST	None
EXPLOSION SAFETY CATEGORY FOR GAS	None
SAFETY PERFORMANCE LEVEL (EN ISO 13849-1)	None
SIL (IEC 61508)	None
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACT ENERGIZED OUTPUTS WITH SIGNALLING FUNCTION	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF OUTPUTS (PROTECTED CONTACT ENERGIZED)	0
NUMBER OF OUTPUTS (PROTECTED SEMICONDUCTOR)	0
NUMBER OF OUTPUTS (SEMICONDUCTOR WITH SIGNALING FUNCTION)	1
OPERATIONAL CURRENT (IB) IN THE SWITCHED STATE AT 24 V DC	25 A
FUNCTIONS	Protection against polarity reversal Protection against wire breakage Short-circuit protection
VOLTAGE TYPE	DC

□□

□□□□□	IL05301007Z
□□	eaton-proximity-switches-e52-proximity-switch-dimensions.eps

MOUNTING METHOD	Non-flush mounting
MATERIAL	Zinc (Insulated)
CONNECTION TYPE	Plug-in connection M12 x 1 4-wire
INSTALLATION TYPE	Not flat
DEGREE OF PROTECTION	IP67 NEMA 4X, 6, 13
INTERFACE TYPE	None
LED INDICATOR	Status indication of Operating voltage: Green LED Status indication of Switching state: Red LED
SWITCH FUNCTION TYPE	Anticoincidence
LOAD CURRENT	Max. 300 mA (I _e)
RESIDUAL CURRENT	0.15 mA (through the load in the blocked state at 230 V AC and 24 V DC)
SHOCK RESISTANCE	30 g, Mechanical, Shock duration 11 ms
SWITCHING FREQUENCY	100 Hz
VOLTAGE RATING - MAX	48 V
WIDTH SENSOR	40 mm
PRODUCT CATEGORY	E52 Cube Series
SWITCHING OUTPUT TYPE	NPN
TEMPERATURE DRIFT OF SN	10 %
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	48 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	6 V
RATED SWITCHING DISTANCE (SN) - MAX	40 mm
REPEATABILITY	2 %
SENSOR HEIGHT	40 mm
SENSOR LENGTH	40 mm
SUPPLY VOLTAGE - MAX	48 V
SUPPLY VOLTAGE - MIN	6 V
SWITCHING HYSTERESIS OF SN	15 %
VOLTAGE DROP (UD)	2.5 V

