



Eaton 135819

Eaton Moeller® series E55 Proximity switch, inductive, 1N/O, Sn=4mm, 3L, 10-30VDC, NPN, M12, insulated material, line 2m

□□□□

PRODUCT NAME	Eaton Moeller® series E55 Proximity switch
CATALOG NUMBER	135819
PRODUCT LENGTH/DEPTH	165.1 mm
PRODUCT HEIGHT	12.7 mm
PRODUCT WIDTH	139.7 mm
PRODUCT WEIGHT	0.14 kg
CERTIFICATIONS	CE IEC/EN 60947-5-2

□□□□	
TYPE	Inductive sensor
ELECTRIC CONNECTION TYPE	Cable
ENCLOSURE MATERIAL FINISHING	Other
ACTUATION TYPE	Metallic Target
ENCLOSURE MATERIAL	Plastic
ENCLOSURE TYPE	Cylinder, screw-thread
CATEGORY (EN 954-1)	B
EXPLOSION SAFETY CATEGORY FOR DUST	None
EXPLOSION SAFETY CATEGORY FOR GAS	None
SAFETY PERFORMANCE LEVEL (EN ISO 13849-1)	None
SIL (IEC 61508)	None
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
DIAMETER SENSOR	12 mm
NUMBER OF CONTACT ENERGIZED OUTPUTS WITH SIGNALLING FUNCTION	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF OUTPUTS (PROTECTED CONTACT ENERGIZED)	0
NUMBER OF OUTPUTS (PROTECTED SEMICONDUCTOR)	0
NUMBER OF OUTPUTS (SEMICONDUCTOR WITH SIGNALING FUNCTION)	1
OPERATIONAL CURRENT (IB) IN THE SWITCHED STATE AT 24 V DC	3 A
OUTPUT CURRENT AT PROTECTED OUTPUT - MAX	0 mA
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
FUNCTIONS	Short-circuit protection Protection against polarity reversal

□□	
□□□□□	IL05301005Z
□□	eaton-proximity-switches-e55-proximity-switch-dimensions.eps

VOLTAGE TYPE	DC
MOUNTING METHOD	Non-flush mounting
MATERIAL	Insulated material
CONNECTION TYPE	3-wire 2 m connection cable
INSTALLATION TYPE	Not flat
DEGREE OF PROTECTION	IP66 NEMA 4X, 13
INTERFACE TYPE	None
LED INDICATOR	Status indication of Switching state: Red LED
SWITCH FUNCTION TYPE	Normally open contact
LOAD CURRENT	Max. 200 mA (I _e)
RESIDUAL RIPPLE	10 % (U _e)
SHOCK RESISTANCE	30 g, Mechanical, Shock duration 11 ms
SUPPLY FREQUENCY	50 Hz, Input, min. Range 60 Hz, Input, max. Range
SWITCHING FREQUENCY	1000 Hz
VOLTAGE RATING - MAX	30 V
WIDTH SENSOR	0 mm
PRODUCT CATEGORY	E55 Limit Switch Style Series
SWITCHING OUTPUT TYPE	NPN
TEMPERATURE DRIFT OF SN	10 %
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	30 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	10 V
RATED SWITCHING DISTANCE (SN) - MAX	4 mm
REPEATABILITY	10 %
SENSOR HEIGHT	0 mm
SENSOR LENGTH	55 mm
SUPPLY VOLTAGE - MAX	30 V

SUPPLY VOLTAGE - MIN	10 V
SWITCHING HYSTERESIS OF SN	20 %
VOLTAGE DROP (UD)	8 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
 Eaton House
 30 Pembroke Road
 Dublin 4, 0000
 Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

