



□□□□□

Eaton 142267

Eaton Moeller series NZM - Molded Case Circuit Breaker. Switch-disconnector 4p 400A 1000VDC

□□□□

PRODUCT NAME	Eaton Moeller series NZM switch-disconnector
CATALOG NUMBER	142267
PRODUCT LENGTH/DEPTH	166 mm
PRODUCT HEIGHT	275 mm
PRODUCT WIDTH	185 mm
PRODUCT WEIGHT	7.3 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC

AMPERAGE RATING	400 A
VOLTAGE RATING	1000 V - 1000 V
CIRCUIT BREAKER FRAME TYPE	N3
FEATURES	Version as main switch Version as emergency stop installation Motor drive optional Remote operation with shunt releases / remote operator Version as maintenance-/service switch
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-021.eps](#)

[eaton-circuit-breaker-terminals-nzm-switch-disconnector-3d-drawing-003.eps](#)

[eaton-circuit-breaker-nzm-switch-disconnector-3d-drawing-002.eps](#)

[eaton-circuit-breaker-terminals-nzm-switch-disconnector-3d-drawing-002.eps](#)

[eaton-circuit-breaker-nzm-switch-disconnector-3d-drawing-003.eps](#)

[eaton-circuit-breaker-nzm-switch-disconnector-3d-drawing.eps](#)

[eaton-circuit-breaker-cable-nzm-mccb-3d-drawing-003.eps](#)

[eaton-circuit-breaker-terminals-nzm-switch-disconnector-3d-drawing.eps](#)

	entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Ground mounting Built-in device fixed built-in technique Distribution board installation Fixed Intermediate mounting
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	96 W
UTILIZATION CATEGORY	DC-22 A
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	6.6 kA
DEGREE OF PROTECTION	IP20
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
AMBIENT OPERATING TEMPERATURE - MAX	70 °C

AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
CURRENT RATING (IU) AT 40°C WITH TERMINAL JUMPERS	400 A
CURRENT RATING (IU) AT 65°C WITH TERMINAL JUMPERS	400 A
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
RATED INSULATION VOLTAGE (UI)	1250 V
RATED OPERATING POWER AT AC-23, 400 V	0 kW
RATED OPERATING POWER AT AC-3, 400 V	0 kW
SWITCH POSITIONS	I, +, 0
LIFESPAN, MECHANICAL	15000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	400 A (DC 22-A)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP20
NUMBER OF POLES	Four-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)
	Max. 8 segments of 24 mm x 1 mm (2x) at box terminal Min. 6 segments of 16 mm x 0.8 mm at box terminal Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched) 10 segments of 50 mm x 1 mm (2x) at rear-side width extension Max. 10 segments of 24

	mm x 1 mm + 5 segments of 24 mm x 1 mm
HANDLE COLOR	Black
FUNCTIONS	Photovoltaic applications Voltage release optional Disconnectors/main switches Interlockable
TYPE	DC switch-disconnector Switch-disconnector
SPECIAL FEATURES	IEC/EN 60947-3 CCC China Compulsory Certificate Main switch characteristics including positive drive to IEC/EN 60204 and VDE 0113. Isolating characteristics to IEC/EN 60947-3 and VDE 0660. N switch-disconnectors can be combined with NZM...- XU, NZM...-XA shunt releases and auxiliary contacts as well as with NZM...-XR... remote operator. For DC switching, all 4 contacts must be connected in series. Refer to the information on jumper kit accessories. Supplied as standard: Screw connection box terminal optional. When working with ungrounded systems (e.g., IT), the installation must ensure that a double ground fault will be impossible. Switch can not be combined with plug- in/withdrawable units and/or connection on rear. N4-4-...-S15-DC feeder unit and outgoer from the bottom only. Lifespan, mechanical: of which max. 50 % trip by shunt/undervoltage release Rated current = rated uninterrupted current: 400 A Values for rated uninterrupted current at 65 °C include jumpers.
APPLICATION	Open areas Utility buildings
NUMBER OF SWITCHES	1
RATED CONDITIONAL	0 kA

SHORT-CIRCUIT CURRENT (IQ)	
RATED CONDITIONAL SHORT-CIRCUIT CURRENT WITH BACK-UP FUSE	2 x 250 AgR 15 kA at 1000 V
RATED OPERATING VOLTAGE (UE) AT AC - MAX	0 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	400 A
RATED PERMANENT CURRENT AT AC-21, 400 V	0 A
RATED PERMANENT CURRENT AT AC-23, 400 V	0 A
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	6.6 kA
SWITCHING POWER AT 400 V	0 kW
HANDLE TYPE	Rocker lever
NUMBER OF OPERATIONS PER HOUR - MAX	60
STANDARD TERMINALS	Screw terminal
SHORT-CIRCUIT PROTECTIVE DEVICE FUSES - MAX	2 x 250 A gR
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 10 mm x 50 mm (2x) at rear-side width extension M10 at rear-side screw connection Min. 20 mm x 5 mm direct at switch rear-side connection Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	16 mm ² (2x) at box terminal 16 mm ² (2x) direct at switch rear-side connection 16 mm ² (1x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	35 mm ² - 240 mm ² (1x) at box terminal 50 mm ² - 240 mm ² (1x) at

2-hole tunnel terminal
25 mm² - 240 mm² (2x)
direct at switch rear-side
connection
50 mm² - 240 mm² (2x) at
2-hole tunnel terminal
25 mm² - 185 mm² (1x) at
tunnel terminal
25 mm² - 120 mm² (2x) at
box terminal
25 mm² - 240 mm² (1x)
direct at switch rear-side
connection

**TERMINAL CAPACITY
(ALUMINUM STRANDED
CONDUCTOR/CABLE)**

25 mm² - 185 mm² (1x) at
tunnel terminal

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the
latest product and support
information.

