



□□□□

Eaton 149887

IZMX40N4-A12F. Circuit-breaker, 4p, 1250A, fixed

□□□□

PRODUCT NAME	Eaton Moeller series IZMX/INX circuit-breaker
CATALOG NUMBER	149887
PRODUCT LENGTH/DEPTH	584 mm
PRODUCT HEIGHT	597 mm
PRODUCT WIDTH	521 mm
PRODUCT WEIGHT	56 kg
COMPLIANCES	IEC IEC/EN 60947



Powering Business Worldwide

AMPERAGE RATING	1250 A
FEATURES	Complete device with protection unit Motor drive optional
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

[eaton-circuit-breaker-mounting-izmx-inx-mccb-dimensions.eps](#)

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Switched-off indicator
FRAME	IZMX40
POLLUTION DEGREE	3
RATED UNINTERRUPTED CURRENT (IU)	1250 A
UTILIZATION CATEGORY	B
MOUNTING METHOD	Fixed
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	60 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	12 kV AC
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Rail connection
ACTUATOR TYPE	Push button
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MAX	0 A
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN	0 A

ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MAX	15000 A
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	2500 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
HEAT DISSIPATION AT RATED CURRENT WITH FIXED MOUNTING	60 W
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF STANDARD MECHANICAL OPERATIONS PER HOUR - MAX	60
OPERATING SEQUENCE UP TO 690 V, 50/60 HZ (IEC/EN 60947)	75 kA
OVERLOAD RELEASE CURRENT SETTING - MAX	1250 A
OVERLOAD RELEASE CURRENT SETTING - MIN	625 A
RATED INSULATION VOLTAGE (UI)	1000 V
OVERVOLTAGE CATEGORY	III
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	2500 A
WEIGHT OF FIXED MOUNTING VERSION (3-POLE)	43 kg
WEIGHT OF FIXED MOUNTING VERSION (4-POLE)	56 kg
PROTECTION	System protection

VOLTAGE RATING AT AC	690 V AC
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	15000 A
NUMBER OF POLES	Four-pole
DEGREE OF PROTECTION	IP41 with door sealing frame IP55 with protective cover IP20
CLOSING DELAY VIA SPRING RELEASE	35 ms

TYPE

- Air circuit breakers/switch-disconnector
- Open circuit breaker

SPECIAL FEATURES

- Optionally fittable by user with comprehensive accessories
- Terminal capacity hint: These are values used in separate switchgear. The actual values will depend on the temperature around the circuit breaker, which is influenced by the ambient temperature, the degree of protection (IP), the mounting height, the partitions, and any external ventilation. Depending on the specific switchgear design, this may result in derating, which can then be compensated for by increasing the cross-sectional area. Temperature rise tests in the specific switchgear can provide specific and detailed information.

POSITION OF Back side

**CONNECTION FOR MAIN
CURRENT CIRCUIT**

RELEASE SYSTEM	Electronic release
SUITABLE FOR	Main conducting paths with 57.6 kA in IT electrical power networks up to U = 440 V
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	240 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	1250 A
RATED SHORT-CIRCUIT BREAKING CAPACITY AT 400 V, 50 HZ	85 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 440 V, 50/60 HZ	187 kA
RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 690 V, 50/60 HZ	166 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	85 kA
RATED SHORT-TIME WITHSTAND CURRENT AT 50/60 HZ (T = 3 S)	66 kA
RATED UNINTERRUPTED CURRENT (IU) AT 50°C	1250 A
RATED UNINTERRUPTED CURRENT (IU) AT 60°C	1250 A
RATED UNINTERRUPTED CURRENT (IU) AT 70°C	1250 A
TERMINAL CAPACITY (COPPER BAR)	60 mm x 10 mm (1x) for fixed mounting (black)
