

Eaton 166414

Eaton Moeller series NZM - Molded Case Circuit Breaker. Switch-disconnector 4p 1000A 1500VDC

PRODUCT NAME	Eaton Moeller series NZM switch-disconnector
CATALOG NUMBER	166414
PRODUCT LENGTH/DEPTH	401 mm
PRODUCT HEIGHT	207 mm
PRODUCT WIDTH	280 mm
PRODUCT WEIGHT	22.656 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC

AMPERAGE RATING	1000 A
VOLTAGE RATING	1500 V - 1500 V
CIRCUIT BREAKER FRAME TYPE	N4
FEATURES	Version as maintenance- /service switch Version as main switch Remote operation with shunt releases / remote operator Motor drive optional Version as emergency stop installation
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV)	Meets the product standard's requirements.

DECLARATIONS OF CONFORMITY	DA-DC-03 N4
	eaton-circuit-breaker-nzm-switch-disconnector-dimensions.eps eaton-circuit-breaker-cable-nzm-mccb-3d-drawing-004.eps eaton-circuit-breaker-terminals-nzm-switch-disconnector-3d-drawing.eps eaton-circuit-breaker-terminals-nzm-switch-disconnector-3d-drawing-002.eps eaton-circuit-breaker-nzm-switch-disconnector-3d-drawing-003.eps eaton-circuit-breaker-nzm-switch-disconnector-3d-drawing-002.eps

RADIATION	
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Built-in device fixed built-in technique Distribution board installation Intermediate mounting Fixed Ground mounting
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	148 W
UTILIZATION CATEGORY	DC-22 A
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	34 kA
DEGREE OF PROTECTION	IP20

ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
CURRENT RATING (IU) AT 40°C WITH TERMINAL JUMPERS	1000 A
CURRENT RATING (IU) AT 65°C WITH TERMINAL JUMPERS	1000 A
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
RATED INSULATION VOLTAGE (UI)	1500 V
RATED OPERATING POWER AT AC-23, 400 V	0 kW
RATED OPERATING POWER AT AC-3, 400 V	0 kW
SWITCH POSITIONS	I, +, 0
LIFESPAN, MECHANICAL	10000 operations
OVERVOLTAGE CATEGORY	III
RATED OPERATIONAL CURRENT	1000 A (DC 22-A)
DEGREE OF PROTECTION (IP), FRONT SIDE	IP20
NUMBER OF POLES	Four-pole
TERMINAL CAPACITY (COPPER STRIP)	10 segments of 50 mm x 1 mm (2x) at 1-hole module plate Max. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched) 10 segments of 80 mm x 1

	mm (2x) at rear-side width extension Max. 10 segments of 32 mm x 1 mm (2x) at flat conductor terminal Min. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched) Min. 6 segments of 16 mm x 0.8 mm at flat conductor terminal
HANDLE COLOR	Black
FUNCTIONS	Photovoltaic applications Disconnectors/main switches Interlockable Voltage release optional
TYPE	DC switch-disconnector Switch-disconnector
SPECIAL FEATURES	IEC/EN 60947-3 CCC China Compulsory Certificate Main switch characteristics including positive drive to IEC/EN 60204 and VDE 0113. Isolating characteristics to IEC/EN 60947-3 and VDE 0660. N switch-disconnectors can, in addition, be combined with NZM...-XU, NZM...-XA shunt releases and auxiliary contacts as well as with NZM...-XR... remote operator. For DC switching, all 4 contacts must be connected in series. Refer to the information on jumper kit accessories. Supplied as standard: Screw connection box terminal optional. When working with ungrounded systems (e.g., IT), the installation must ensure that a double ground fault will be impossible. Switch can not be combined with plug-in/withdrawable units and/or connection on rear. Lifespan, mechanical: of which max. 50 % trip by shunt/undervoltage release Rated current =

	rated uninterrupted current: 1000 A Values for rated uninterrupted current at 65 °C include jumpers.
APPLICATION	Open areas Utility buildings
NUMBER OF SWITCHES	1
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	0 kA
RATED OPERATING VOLTAGE (UE) AT AC - MAX	0 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	1000 A
RATED PERMANENT CURRENT AT AC-21, 400 V	0 A
RATED PERMANENT CURRENT AT AC-23, 400 V	0 A
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.1 S)	34 kA
SWITCHING POWER AT 400 V	0 kW
HANDLE TYPE	Rocker lever
NUMBER OF OPERATIONS PER HOUR - MAX	60
STANDARD TERMINALS	Screw terminal
TERMINAL CAPACITY (COPPER BUSBAR)	<p>Max. 50 mm x 10 mm (2x) direct at switch rear-side connection</p> <p>Min. 25 mm x 5 mm direct at switch rear-side connection</p> <p>50 mm x 10 mm (2x) at rear-side 2-hole module plate</p> <p>Min. 25 mm x 5 mm at rear-side 1-hole module plate</p> <p>M10 at rear-side screw connection</p> <p>Max. 10 mm x 80 mm (2x) at rear-side width extension</p> <p>Max. 80 mm x 10 mm (2x) direct at switch rear-side connection</p>

	Min. 60 mm x 10 mm at rear-side width extension Max. 50 mm x 10 mm (2x) at rear-side 1-hole module plate
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	95 mm ² - 240 mm ² (6x) at rear-side width extension 120 mm ² - 300 mm ² (1x) at rear-side 1-hole module plate 50 mm ² - 240 mm ² (4x) at 4-hole tunnel terminal 35 mm ² - 185 mm ² (4x) at rear-side 2-hole module plate 300 mm ² (4x) at rear-side width extension 95 mm ² - 185 mm ² (2x) at rear-side 2-hole module plate 95 mm ² - 300 mm ² (2x) at rear-side 1-hole module plate
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	50 mm ² - 185 mm ² (4x) direct at switch rear-side connection 120 mm ² - 185 mm ² (1x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	50 mm ² - 240 mm ² (4x) at 4-hole tunnel terminal

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

