



□□□□

## Eaton 149888

IZMX40N4-A16F. Circuit-breaker, 4p, 1600A, fixed

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series IZMX/INX circuit-breaker
<b>CATALOG NUMBER</b>	149888
<b>PRODUCT LENGTH/DEPTH</b>	584 mm
<b>PRODUCT HEIGHT</b>	597 mm
<b>PRODUCT WIDTH</b>	521 mm
<b>PRODUCT WEIGHT</b>	56 kg
<b>COMPLIANCES</b>	IEC IEC/EN 60947



Powering Business Worldwide

<b>AMPERAGE RATING</b>	1600 A
<b>FEATURES</b>	Motor drive optional Complete device with protection unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF</b>	Does not apply, since the entire switchgear needs to

<b>ASSEMBLIES</b>	be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Switched-off indicator
<b>FRAME</b>	IZMX40
<b>POLLUTION DEGREE</b>	3
<b>RATED UNINTERRUPTED CURRENT (IU)</b>	1600 A
<b>UTILIZATION CATEGORY</b>	B
<b>MOUNTING METHOD</b>	Fixed
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	100 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	12 kV AC
<b>DEVICE CONSTRUCTION</b>	Built-in device fixed built-in technique
<b>DIRECTION OF INCOMING SUPPLY</b>	As required
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Rail connection
<b>ACTUATOR TYPE</b>	Push button
<b>ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MAX</b>	0 A
<b>ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN</b>	0 A

<b>ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MAX</b>	19200 A
<b>ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MIN</b>	3200 A
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>HEAT DISSIPATION AT RATED CURRENT WITH FIXED MOUNTING</b>	100 W
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	2
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>NUMBER OF STANDARD MECHANICAL OPERATIONS PER HOUR - MAX</b>	60
<b>OPERATING SEQUENCE UP TO 690 V, 50/60 HZ (IEC/EN 60947)</b>	75 kA
<b>OVERLOAD RELEASE CURRENT SETTING - MAX</b>	1600 A
<b>OVERLOAD RELEASE CURRENT SETTING - MIN</b>	800 A
<b>RATED INSULATION VOLTAGE (UI)</b>	1000 V
<b>OVERVOLTAGE CATEGORY</b>	III
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	3200 A
<b>WEIGHT OF FIXED MOUNTING VERSION (3-POLE)</b>	43 kg
<b>WEIGHT OF FIXED MOUNTING VERSION (4-POLE)</b>	56 kg
<b>PROTECTION</b>	System protection

<b>VOLTAGE RATING AT AC</b>	690 V AC
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	19200 A
<b>NUMBER OF POLES</b>	Four-pole
<b>DEGREE OF PROTECTION</b>	IP41 with door sealing frame IP20 IP55 with protective cover
<b>CLOSING DELAY VIA SPRING RELEASE</b>	35 ms
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Air circuit breakers/switch-disconnector</li> <li>• Open circuit breaker</li> </ul>
<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• Optionally fittable by user with comprehensive accessories</li> <li>• Terminal capacity hint: These are values used in separate switchgear. The actual values will depend on the temperature around the circuit breaker, which is influenced by the ambient temperature, the degree of protection (IP), the mounting height, the partitions, and any external ventilation. Depending on the specific switchgear design, this may result in derating, which can then be compensated for by increasing the cross-sectional area. Temperature rise tests in the specific switchgear can provide specific and detailed information.</li> </ul>
<b>POSITION OF</b>	Back side

---

**CONNECTION FOR MAIN  
CURRENT CIRCUIT**

---

<b>RELEASE SYSTEM</b>	Electronic release
<b>SUITABLE FOR</b>	Main conducting paths with 57.6 kA in IT electrical power networks up to U = 440 V
<b>RATED OPERATING VOLTAGE (UE) - MAX</b>	690 V
<b>RATED OPERATING VOLTAGE (UE) - MIN</b>	240 V
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	1600 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY AT 400 V, 50 HZ</b>	85 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 440 V, 50/60 HZ</b>	187 kA
<b>RATED SHORT-CIRCUIT MAKING CAPACITY UP TO 690 V, 50/60 HZ</b>	166 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>	85 kA
<b>RATED SHORT-TIME WITHSTAND CURRENT AT 50/60 HZ (T = 3 S)</b>	66 kA
<b>RATED UNINTERRUPTED CURRENT (IU) AT 50°C</b>	1600 A
<b>RATED UNINTERRUPTED CURRENT (IU) AT 60°C</b>	1600 A
<b>RATED UNINTERRUPTED CURRENT (IU) AT 70°C</b>	1600 A
<b>TERMINAL CAPACITY (COPPER BAR)</b>	80 mm x 10 mm (1x) for fixed mounting (black)

---

