



Eaton 158314

Eaton Moeller series xPole (Style 5) - mMCT MCB. Circuit-breaker, 63 A, 2p, Type C characteristic

□□□□

PRODUCT NAME	Eaton Moeller series xPole (Style 5) - mMCT MCB
CATALOG NUMBER	158314
PRODUCT LENGTH/DEPTH	90 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	0.47 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

□□□□

USED WITH	mMCT Miniature circuit breaker
AMPERAGE RATING	63 A
FEATURES	Additional equipment possible
ACCESSORIES REQUIRED	ZP-IHK 286052
FITTED WITH:	Z-IS/SPE-1TE 274418
FRAME	45 mm
POLLUTION DEGREE	2
LIFESPAN, MECHANICAL	20000 operations
MOUNTING METHOD	Quick attachment with 3 latch positions for top-hat rail IEC/EN 60715
DEGREE OF PROTECTION	IP20
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	10.4 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
BUSBAR MATERIAL THICKNESS	0.8 mm - 2 mm
TRIPPING CHARACTERISTIC	C
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	75 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	50 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	2.5 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	50 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	2.5 mm ²
CURRENT LIMITING CLASS	3
FREQUENCY RATING - MAX	60 Hz

□□

CHARACTERISTIC CURVE	eaton-xpole-mmct-mcb-characteristic-curve.jpg
PEP ECO-PASSPORT	eaton-non-selective-universal-mcb-pep-eato-00259-v0101-en.pdf
□□□	eaton-xpole-mmct4-6-m-mcb-wiring-diagram-003.jpg
□□	eaton-xpole-mmct-mcb-dimensions.jpg eaton-xpole-mmct-mcb-3d-drawing-002.jpg eaton-xpole-mmct-mcb-3d-drawing.jpg

FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	5.2 W
WIDTH IN NUMBER OF MODULAR SPACINGS	3
VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Two-pole
LIFESPAN, ELECTRICAL	10000 operations
RELEASE CHARACTERISTIC	C

TYPE

- Miniature circuit breaker
- mMCT

SPECIAL FEATURES

- Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
- Tripping signal contact for subsequent installation ZP-NHK 248437

APPLICATION

Switchgear for industrial and advanced commercial applications

NUMBER OF POLES (PROTECTED)	2
NUMBER OF POLES (TOTAL)	2
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	63 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V	25 kA
RATED SHORT-CIRCUIT	25 kA

