



Eaton 160D200Q

Eaton Bussmann series Fuse-link, low voltage, 160 A, AC 500 V, D5, 56 x 46 mm, gR, DIN, IEC, fast-acting

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	160D200Q
PRODUCT LENGTH/DEPTH	56 mm
PRODUCT HEIGHT	46 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	224.6 g
COMPLIANCES	CE RoHS Compliant CE Marked
CERTIFICATIONS	IEC/EN 60269-3 VDE 0636 IEC 60269 DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301

□□□□

AMPERAGE RATING	160 A
FUSE SIZE	DV
CURRENT TYPE	AC
BREAKING CAPACITY	50 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
CONSTRUCTION SIZE (FUSE INSERTS)	DV
RATED VOLTAGE AC	500 V
FUSE TYPE	D200Q - Fast acting
ACCESSORY/SPARE PART TYPE	160GD200 Copper screw cap gauge piece
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
COLOR	Copper
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Other
CONSTRUCTION SIZE	DV
FUSE SHAPE	Bottle
RESPONSE TIME	Fast-acting
VOLTAGE TYPE	AC
SUITABLE FOR	R2/DV Fuse base
MATERIAL	White ceramic body
RELEASE CHARACTERISTIC	Fast (F)
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	For domestic and general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other
RATED SWITCHING CAPACITY AC	50 kA

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

