

Eaton 160MT

Eaton Bussmann series high speed British standard fuse, Single barrel, 160A, 690 VAC/350 VDC (IEC), 700 VAC (UL), Class aR, Breaking capacity 200 kA RMS Sym., 40 kA DC at 350 VDC (IEC)

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	160MT
UPC	051712831611
PRODUCT LENGTH/DEPTH	46 mm
PRODUCT HEIGHT	45 mm
PRODUCT WIDTH	115 mm
PRODUCT WEIGHT	256 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated Designed and tested to BS88 part 4 IEC 60269-4 UL recognized

AMPERAGE RATING	160 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	350 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	84 mm
MOUNTING DIMENSION	M8
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I2T)	15000 at 415 V, 25000 at 660 V
WATT LOSSES	26 W
FUSE SHAPE	Offset bolted tags
PRE ARC (I2T)	2400
COLOR	None
INTERRUPT RATING	200 kA RMS Sym (IEC/UL), 40 kA at 350 Vdc (IEC)
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	MT
SUITABLE FOR	MC-700 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
FUSE SYSTEM	Other



(ACCORDING TO IEC
60269)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

