

## Eaton 168255

Eaton Moeller series xEffect - FRBdM RCBO - residual-current circuit breaker with overcurrent protection. RCD/MCB, 16A, 10mA, MCB trip type C, 1-phase+N, RCCB trip type: A

|                             |                                                                                                          |
|-----------------------------|----------------------------------------------------------------------------------------------------------|
|                             |                                                                                                          |
| <b>PRODUCT NAME</b>         | Eaton Moeller series xEffect - FRBdM RCBO - residual-current circuit breaker with overcurrent protection |
| <b>CATALOG NUMBER</b>       | 168255                                                                                                   |
| <b>PRODUCT LENGTH/DEPTH</b> | 86 mm                                                                                                    |
| <b>PRODUCT HEIGHT</b>       | 75 mm                                                                                                    |
| <b>PRODUCT WIDTH</b>        | 37 mm                                                                                                    |
| <b>PRODUCT WEIGHT</b>       | 0.25 kg                                                                                                  |
| <b>COMPLIANCES</b>          | CE Marked<br>RoHS conform                                                                                |
| <b>CERTIFICATIONS</b>       | CE                                                                                                       |

## Delivery Program

|                                                               |                                                                                                |
|---------------------------------------------------------------|------------------------------------------------------------------------------------------------|
| <b>BASIC FUNCTION</b>                                         | Combined RCD/MCB devices                                                                       |
| <b>NUMBER OF POLES (TOTAL)</b>                                | 2                                                                                              |
| <b>TRIPPING CHARACTERISTIC</b>                                | C                                                                                              |
| <b>TYPE</b>                                                   | RCBO                                                                                           |
| <b>APPLICATION</b>                                            | Switchgear for industrial and advanced commercial applications                                 |
| <b>TRIPPING CHARACTERISTIC</b>                                | C                                                                                              |
| <b>TYPE</b>                                                   | RCBO                                                                                           |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                 | Does not apply, since the entire switchgear needs to be evaluated.                             |
| <b>SENSITIVITY TYPE</b>                                       | Pulse-current sensitive                                                                        |
| <b>10.11 SHORT-CIRCUIT RATING</b>                             | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b> | Does not apply, since the entire switchgear needs to be evaluated.                             |

## Technical Data - Electrical

|                                |                         |
|--------------------------------|-------------------------|
| <b>SENSITIVITY TYPE</b>        | Pulse-current sensitive |
| <b>TRIPPING CHARACTERISTIC</b> | C                       |

## Technical Data

**10.2.5 LIFTING** Does not apply, since the entire switchgear needs to be evaluated.

**CURRENT LIMITING CLASS** 3

**RATED SWITCHING CAPACITY (IEC/EN 61009)** 10 kA

**RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60947-2)** 0 kA

**DISCONNECTION CHARACTERISTIC** Short-time delayed

**10.10 TEMPERATURE RISE** The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**WIDTH IN NUMBER OF MODULAR SPACINGS** 2

**HEAT DISSIPATION CAPACITY** 0 W

**10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT** Meets the product standard's requirements.

**POLLUTION DEGREE** 2

**10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH** Is the panel builder's responsibility.

**CHARACTERISTIC CURVE** [eaton-xeffect-frbdm-characteristic-curve.jpg](#)

[eaton-xeffect-frbdm-wiring-diagram.jpg](#)

[eaton-xeffect-digital-switchgear-brochure-br003004en-en-us.pdf](#)

[eaton-xeffect-digital-circuit-breaker-brochure-br003004en-en-us.pdf](#)

[eaton-xeffect-frbdm-rcbo-catalog-ca003013en-en-us.pdf](#)

[eaton-xeffect-frbdm-dimensions.jpg](#)

[eaton-xeffect-frbdm-3d-drawing-002.jpg](#)

[eaton-xeffect-frbdm-3d-drawing-005.jpg](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

